








PIN DEFINE TABLE			
PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11	—	B2	—
A10	—	B3	—
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D-	B6	D+
A6	D+	B7	D-
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3	—	B10	—
A2	—	B11	—
A1	GND	B12	GND

- SPECIFICATION:
1. MATERIAL & FINISH:SEE THE LIST;
 2. PLATING SPECIFICATION:
 - 2-1.CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE MATING AREA OF CONTACT.
Au PLATED ON THE SOLDER AREA.
 - 2-2.SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.
 - 2-3.MID PLATE:CLEAR ONLY
 3. MECHANICAL:
 - 3.1.MATING FORCE:0.5~2.0kgf;
 - 3.2.UNMATING FORCE:0.8~2.0kgf.
 - 0.6~2.0kgf AFTER DURABILITY TEST;
 - 3.3.DURABILITY:10000 CYCLES;
 - 4.ELECTRICAL:
 - 4.1.CURRENT RATING:5A Max;
 - 4.2.VOLTAGE RATING:20V Max;
 - 4.3.DIELECTRIC WITHSTANDING VOLTAGE:100VAc;
 - 4.4.CONTACT RESISTANCE:40mΩ Ohms Max.;
 - 4.5.INSULATION RESISTANCE:100M Ohms Min.;
 - 5.ENVIRONMENTAL:
 - 5.1.OPERATING TEMPERATURE:-40°C~+85°C;
 - 5.2.WETTING TEMPERATURE:265±5°C,5±0.5s
 - 5.3.Salt Spray Test:48H Min



(TOP VIEW)
RECOMMENDED P.C.B. LAYOUT (T:0.8mm)
TOLERANCE UNSPECIFIED ±0.05mm

NO.	PART NAME	Q'TY	MATERIAL	FINISH
5	CAP	1	High temperature plastic	UL94 V-0,Black
4	Shell	1	Stainless Steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless Steel,T=0.15mm	No Plating
2	Contact	16	Copper Alloy,T=0.15mm	Au/Ni-Plated
1	Housing	1	High temperature plastic	UL94 V-0,Black

MANUFACTURE DWG



东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd

UNLESS OTHERWISE
SPECIFIED TOLERANCES

TITLE:
TYPE-C 16p 立贴式母座H10.0mm

PAR	TYPE-C-627-LSCH100
-----	--------------------

DECIMALS:

ANGLES:

X.:±0.50

X':±5°

X.X:±0.35

X.X':±3°

X.XX:±0.25

X.XX':±2.5°

CUSTOMER COPY



DWN	Lucas
-----	-------

CHKD	Ethan
------	-------

APVD	Jacob
------	-------

SCALE:1:1	UNIT:MM
-----------	---------

SIZE:A4	SHEET:1F2	REV:A
---------	-----------	-------



说明:

1. 每卷前后各空10PCS,尾部用美纹胶纸封住;
2. 将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
3. 每10卷盘一叠共2500Pcs并装入1个外箱内;
4. 在搬运过程中要轻拿轻放;
5. 在运输中不可堆放过多(1.8M最高),不可重压;
6. 跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a. 产品不可跑下带凹槽;
b. 产品不可有摔伤,变形;
c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
①	TYPE C RECEPTACLE		2500PCS/CARTON
②	CARRIER TAPE	W=24mm,T=0.50mm	250PCS/PLATE
③	COVER TAPE	W=21.3mm	10PLATES/CARTON
④	REEL PLATE	φ330*100*24.4mm	10PCS/CARTON
⑤	RoHS LABEL		10PCS/CARTON
⑥	PRODUCT LABER		10PCS/CARTON
⑦	CARTON	350*340*310mm	1PCS/PACKAGE

MANUFACTURE DWG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

X.:±0.50

X.X:±0.35

X.XX:±0.25

ANGLES:

X.:±5°

X.X':±3°

X.XX':±2.5°

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd

TITLE:

TYPE-C 16p 立贴式每座H10.0mm

PAR

TYPE-C-627-LSCH100

DWN

Lucas

CHKD

Ethan

APVD

Jacob

SCALE1:1

UNIT:MM

SIZE:A4

SHEET:2F2

REV:A

CUSTOMER COPY