










Rev.	ECN Number	Description	Date	Drawn	Checkd	Approved
A	ECN171722	正式A版发行	10/19/17	Gan	PENG	TAN



RECOMMENDED PCB LAYOUT
TOLERANCE $\pm 0.05\text{mm}$
(FOR REFERENCE ONLY)



NOTES:

1:MATERIAL:

1-1: STAINLESS STEEL, T=0.10mm.

2:FINISH:

2-1: 3u" MIN. Au PLATING ON CONTACT AREA,
1u" MIN. Au PLATING ON SOLDER AREA,
50~150u" NICKEL UNDERPLATING OVER ALL.

2-2: DIMENSIONS WITHOUT TOLERANCE PLEASE REFER TO TOLERANCE TABLE,
STRUCTURE WITHOUT DIMENSIONS PLEASE REFER TO 3D DRAWING.

2-3: DIMENSIONS OF PCB PAD AND STENCIL ARE FOR REFERENCE ONLY,
CUSTOMERS CAN MODIFY IT BY THEIR OWN.

3:SPECIFICATIONS:

3-1.RATING CURRENT: 2A.

3-2.RATING VOLTAGE: 10V

3-1.CONTACT RESISTANCE: 50mΩ MAX.

3-2.OPERATING TEMPERATURE: -40°C~+85°C.

3-3.FORCE AT MAX. DEFLECTION: 0.90N MIN ON CONTACT POINT

4.PACKING SPECIFICATION: REEL&TAPE

5.DIMENSIONS MARKED , CPK>1.33



ELECTRIC
CONNECTOR
TECHNOLOGY

GENERAL TOLERANCE

XX. ± 0.50	
X. ± 0.35	X° $\pm 2.0^\circ$
.X ± 0.25	.X° $\pm 1.0^\circ$
.XX ± 0.15	.XX° $\pm 0.5^\circ$

SCALE:


1:1

UNIT:

mm

SIZE:

A4



DRAWN

Gan

CHECK

APPROVE

DATE

10/19/17

DATE

DATE

DWG. NO.

600-11472-01

PARTS NO.(INTENDED USE)

818011472

TITLE

(CUSTOMER DRAWING)

Spring L2.7*W1.2*H2.5mm

REV.

A

SHEET

1/1