






说明:

- 每卷前后各空 10PCS,尾部用美纹胶纸封住;
- 将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上 1Pcs 物料标签;
- 每 10 卷盘一叠共 3500Pcs 并装入 1 个外箱内;
- 在搬运过程中要轻拿轻放;
- 在运输中不可堆放过多(1.8M 最高),不可重压;
- 跌落测试条件:
成品箱从 1.2 米高度自由落体(一角三棱六面):
a. 产品不可跑出下带凹槽;
b. 产品不可有摔伤,变形;
c. 内包装材料不可严重破损。

NO.	NAME	SPEC	Q'TY
0	TYPE C RECEPTACLE		3500PCS/CARTON
1	CARRIER TAPE	W=24mm,T=0.50mm	350PCS/PLATE
2	COVER TAPE	W=21.3mm	10PLATES/CARTON
3	REEL PLATE	$\phi 330*100*24.4$ mm	10PCS/CARTON
4	RoHS LABEL		10PCS/CARTON
5	PRODUCT LABER		10PCS/CARTON
6	CARTON	350*340*310mm	1PCS/PACKAGE

MANUFACTURE DWG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

X.: ± 0.50 X.X: ± 0.35 X.XX: ± 0.25

ANGLES:

X.: $\pm 5^{\circ}$ X.X': $\pm 3^{\circ}$ X.XX': $\pm 2.5^{\circ}$ 东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdTITLE: TYPE-C 立贴式母座
H8.8mm——包装图

PAR	TYPE-C-627-LSCH088-X
DWN	Lucas
CHKD	Ethan
APVD	Jacob
SCALE:1:1	UNIT:MM
SIZE:A4	SHEET:2F2
REV:A	