





RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05



G-Switch RF Specification:
1.Contact Resistance: 20mΩ Max;
2.Dielectric Withstanding Voltage:
200V AC For 1 Minute;
3.Insulation Resistance: 1000MΩ Min;
4.Frequency Range: DC up to 6GHz
Vswr:1.3 Max. at 0~3GHz;
Vswr:1.4 Max. at 3~6GHz;
5.Operating Temperature: -40°Cto +90°C.

ITEM	TITLE	MATERIAL/FINISH
1	TERMINAL	COPPER ALLOY/GOLD PLATED OVER Ni
2	SHELL	PHOSPHOROUS COPPER/Gold PLATED OVER Ni
3	HOUSING	LCP UL94V-0/BLACK



RoHS
Compliant
2002/95/EC



SCALE: 9:1	UNIT: mm
SIZE: A4	
Unless otherwise General Tolerance:	
X.	±0.30
X.x	±0.20
X.xx	±0.15
X.xxx	±0.10
Angles	±3°

Title: RF IV Receptacle Conn
SMT 1.7×1.7×H0.60mm

Molde Code: GT-RF4060A-01G

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2023.10.07

品赞科技®
b-Switch

REV: A0 SHEET: 1/1