

General Description:

The LWN6045ASD uses trench technology and design to provide excellent $R_{DS(ON)}$ with low gate charge. It can be used in a wide variety of applications. The package form is SOP-8, which accords with the ROHS standard and Halogen Free standard.

Features:

- Fast Switching
- Low Gate Charge and $R_{DS(ON)}$
- Low Reverse transfer capacitances

Applications:

- DC-DC converter
- Portable Equipment
- Power Management

100% DVDS Tested

100% Avalanche Tested



Package Marking and Ordering Information:

Marking	Part Number	Package	Packing	Qty.
N6045A/LW SD/D.C.	LWN6045ASD	SOP-8	Reel	4000 Pcs

Absolute Maximum Ratings:


Symbol	Parameter		Value	Units
V_{DSS}	Drain-to-Source Voltage		60	V
I_D	Continuous Drain Current	$T_A=25^{\circ}\text{C}$	6.0	A
	Continuous Drain Current	$T_A=100^{\circ}\text{C}$	3.8	A
I_{DM}^{a1}	Pulsed Drain Current		24	A
E_{AS}^{a2}	Single pulse avalanche energy		27	mJ
V_{GS}	Gate-to-Source Voltage		± 20	V
P_D	Power Dissipation		2.2	W
T_J, T_{STG}	Operating Junction and Storage Temperature Range		150, -55 to 150	$^{\circ}\text{C}$
T_L	Maximum Temperature for Soldering		260	$^{\circ}\text{C}$

Thermal Characteristics:


Symbol	Parameter	Value	Units
$R_{\theta JA}^{a3}$	Thermal Resistance, Junction-to-Ambient	56.8	$^{\circ}\text{C/W}$

V_{DSS}	60	V
I_D	6.0	A
P_D	2.2	W
$R_{DS(ON)}$ TYPE	34	$\text{m}\Omega$

Marking and Pin Assignment



Inner Equivalent Principium Chart



Electrical Characteristic ($T_J = 25\text{ }^{\circ}\text{C}$, unless otherwise specified):

Static Characteristics						
Symbol	Parameter	Test Conditions	Value			Units
			Min.	Typ.	Max.	
V_{DSS}	Drain to Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	60	--	--	V
I_{DSS}	Drain to Source Leakage Current	$V_{DS}=60V, V_{GS}=0V$	--	--	1.0	μA
$I_{GSS(F)}$	Gate to Source Forward Leakage	$V_{GS}=+20V, V_{DS}=0V$	--	--	100	nA
$I_{GSS(R)}$	Gate to Source Reverse Leakage	$V_{GS}=-20V, V_{DS}=0V$	--	--	-100	nA
$V_{GS(TH)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	1.1	1.6	2.1	V
$R_{DS(ON)1}$	Drain-to-Source On-Resistance	$V_{GS}=10V, I_D=5.0A$	--	34	40	m Ω
$R_{DS(ON)2}$	Drain-to-Source On-Resistance	$V_{GS}=4.5V, I_D=3.0A$	--	37	50	m Ω

Dynamic Characteristics						
Symbol	Parameter	Test Conditions	Value			Units
			Min.	Typ.	Max.	
C_{iss}	Input Capacitance	$V_{GS} = 0V$	--	1030	--	pF
C_{oss}	Output Capacitance	$V_{DS} = 30V$	--	42	--	
C_{rss}	Reverse Transfer Capacitance	$f = 1.0MHz$	--	38	--	
R_G	Gate resistance	$V_{GS}=0V, V_{DS}=0V, f=1MHz$	--	1.3	--	Ω



Resistive Switching Characteristics						
Symbol	Parameter	Test Conditions	Value			Units
			Min.	Typ.	Max.	
$t_{d(ON)}$	Turn-on Delay Time	$I_D = 5.0A$	--	8.0	--	ns
t_r	Rise Time	$V_{DS} = 30V$	--	3.6	--	
$t_{d(OFF)}$	Turn-Off Delay Time	$V_{GS} = 10V$	--	19.2	--	
t_f	Fall Time	$R_G = 3.0\Omega$	--	3.2	--	
Q_g	Total Gate Charge	$V_{GS} = 10V$	--	25	--	nC
Q_{gs}	Gate Source Charge	$V_{DS} = 30V$	--	2.6	--	
Q_{gd}	Gate Drain Charge	$I_D = 5.0A$	--	4.8	--	



Source-Drain Diode Characteristics						
Symbol	Parameter	Test Conditions	Value			Units
			Min.	Typ.	Max.	
I_S	Diode Forward Current	$T_A = 25\text{ }^{\circ}\text{C}$	--	--	6.0	A
I_{SM}	Diode Pluse Current		--	--	24	A
V_{SD}	Diode Forward Voltage	$I_S=5.0A, V_{GS}=0V$	--	--	1.2	V

a1: Repetitive rating; pulse width limited by maximum junction temperature

a2: $V_{DD}=30V, L=0.1mH, R_G=25\Omega$, Starting $T_J=25\text{ }^{\circ}\text{C}$

a3: Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 μm thick) copper area for drain connection.

Characteristics Curve:













Figure 13: Max. Transient Thermal Impedance


Test Circuit & Waveform:

Figure 14: Gate Charge Test Circuit & Waveform

Figure 15: Resistive Switching Test Circuit & Waveforms

Figure 16: Unclamped Inductive Switching Test Circuit & Waveforms

Package Outline:


Symbol	Dimensions In Millimeters		
	Min	Ref	Max
A	1.350	1.550	1.750
A1	0.030	0.140	0.250
A2	1.350	1.450	1.550
b	0.330	0.430	0.530
c	0.160	0.205	0.250
D	4.700	5.000	5.300
E	3.800	3.900	4.000
E1	5.800	6.000	6.200
e	1.270(BSC)		
L	0.400	0.835	1.270
θ	0°	4°	8°

Revision History:

Revision	Date	Descriptions
Rev 1.1	Oct.2025	Formal Version

Disclaimer:

The information in this document is believed to be accurate and reliable. However, no responsibility is assumed by LW-Micro for its use. All operating parameters must be designed, validated and tested to ensure they meet the requirements of your application. LW-Micro reserves the right to make any specification and/or circuitry changes without prior notification. Before starting a brand-new project, please contact LW-Micro Sales to get the most recent relevant information.

Mailing Address: Unit 02&04&05, 10th Floor, Building 5, No.666 Shengxia Road, No.122 Yindong Road,
China (Shanghai) Pilot Free Trade Zone
Shanghai Lewa Micro-electronics Technology Co., Ltd