

Features

- Low operating voltage: 9V
- Ultra low capacitance: 0.25pF(Typ)
- Ultra low leakage: nA level
- Low clamping voltage
- -IEC 61000-4-2 (ESD) immunity test
 - Air discharge: $\pm 30\text{kV}$
 - Contact discharge: $\pm 30\text{kV}$
- -IEC61000-4-4 (EFT) 40A (5/50ns)
- -IEC61000-4-5 (Lightning) 6 A (8/20 μs)
- 2-pin leadless package
- These are Pb-Free Devices
- Response Time is Typically < 1 ns


Mechanical Characteristics

- Package: DFN0603-2(0201)
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound
- Terminal Connections: See Diagram Below
- -IEC 61000-4-2 (ESD) immunity test

Applications

- RF antenna
- USB 3.2 Gen 1 and Gen 2
- Ethernet 1000 BASE-T
- Ethernet 10G BASE-T
- Display port

Dimensions and Pin Configuration



Absolute Maximum Ratings (Tamb=25°C unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	100	W
Peak Pulse Current (8/20μs)	Ipp	6	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	VESD	±30 ±30	KV
Operating Temperature Range	TJ	-55 to +125	°C
Storage Temperature Range	Tstg	-55 to +150	°C

Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	VRWM	--	--	9	V	
Breakdown Voltage	VBR	12			V	IT= 1mA
Reverse Leakage Current	IR	--	--	200	nA	VRWM=9V
Clamping Voltage	VC	--	12	15	V	Ipp=1A(8x 20us pulse)
Clamping Voltage	VC	--	16	20	V	Ipp=5.5A(8x 20us pulse)
Junction Capacitance	CJ	--	0.25	0.4	pF	VR = 0V, f = 1MHz

Electrical Characteristics

Symbol	Parameter
VBR	Reverse Breakdown Voltage
IBR	Reverse Breakdown Current
VRWM	Reverse Stand-off Voltage
IR	Reverse Leakage Current
VH	Holding Voltage
IH	Holding Current
VT	Trigger Voltage
IT	Trigger Current
Ipp	Peak Pulse Current
VCL	Clamping Voltage



Characteristic Curves

Fig1. 8/20 μ s Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve




Package Outline & Dimensions

DFN0603-2 (0201)



SYM	DIMENSIONS		
	MILLIMETERS		
	MIN	NOM	MAX
A	0.230	0.300	0.330
A1	0.000	0.020	0.050
b	0.215	0.245	0.275
c	0.120	0.150	0.180
D	0.550	0.600	0.650
e	0.355 BSC		
E	0.250	0.300	0.350
L	0.160	0.190	0.220
h	0.079 BSC		

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
X	0.30	0.012
Y1	0.25	0.010
Y2	0.15	0.006
Y3	0.40	0.016
Z	0.65	0.026