


1. External Dimensions (Unit:m/m)



TYPE	A	B	C	D	E	Q'Ty/ package
DP1519	16.5Max	20.0Max	5.0±1.0	0.8±0.1	7.5±0.5	/

2. Part Number Code

DP 1519 M 220
 A B C D

A: Series Name Choke Coils
 B: Dimensions(mm) 1519: 16.5*20 Max
 C: Tolerance M: ±20%
 D: Inductance 220=22uH

3. Electrical Characteristics

Part Number	Inductance (uH)	Tolerance	Test Frequency (Hz)	DCR(Max) (mΩ)	Heat Rating Current Irms(A)	Saturation Current Isat(A)
DP1519M220	22.0	±20%	1K/0.25V	25.0	8.0	5.0

4. Material List

NO	ITEM	SPECIFICATIONS	SUPPLIER	UL FILE
1	Core	DR2W11*13.5 B8.2	HC OR EQUIVALENT	N/A
		H50 P15.6*19*13	HC OR EQUIVALENT	N/A
2	Wire	2UEWF Φ0.8*11.5Ts Ref	FR OR EQUIVALENT	E196072
3	UL	Φ 12mm Black	CY OR EQUIVALENT	E180908
4	Tin	HB07H	CD OR EQUIVALENT	N/A
5	Epoxy	E-506	LD OR EQUIVALENT	N/A