


Features	Case: SMA(DO-214AC)
<ul style="list-style-type: none"> • Glass Passivated Die Construction • Low forward voltage drop • High current capability • High reliability • Metalsilicon junction, majority carrier conduction • Plastic Case Material has UL Flammability Classification Rating 94V-0 	 <p style="text-align: center;">Dimensions in inches and (millimeters)</p>
Mechanical Data	
<ul style="list-style-type: none"> • Case: Molded plastic SMA • Terminals: Plated leads solderable per MIL-STD-750, Method 2026 guaranteed • Polarity: Color band denotes cathode end • Mounting Position: Any • Making: Type Number 	

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified Single phase, half wave, 60Hz, resistive or inductive load For capacitive load derate current by 20%										
Type Number	SYMBOL	S3A	S3B	S3D	S3G	S3J	S3K	S3M	Unit	
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V	
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	700	V	
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	V	
Average Rectified Output Current @ $T_L = 75^\circ C$	$I_{F(AV)}$	3.0							A	
Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	60							A	
Forward Voltage @ $I_F = 2.0A$ @ $I_F = 3.0A$	V_{FM}	1.0 1.1							V	
Peak Reverse Current @ $T_A = 25^\circ C$	I_R	5.0							uA	
At Rated DC Blocking Voltage @ $T_A = 125^\circ C$		200								
Operating Temperature Range	T_J	-55 to +150							°C	
Storage Temperature Range	T_{STG}	-55 to +150							°C	

Fig. 1 Forward Current Derating Curve




Fig. 2 Typ. Forward Characteristics




Fig. 3 Max Non-Repetitive Peak Fwd Surge Current




Fig.4 Typical Reverse Characteristics





Fig.5 Mounting PAD Layout



Disclaimer

The information presented in this document is for reference only. Chongqing Zhongjing Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Zhongjing or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.