

BCM120S02D3

Silicon Carbide Schottky Diode

1200V, 2A

Description

BCM120S02D3 utilizes Bestirpower’s advanced silicon carbide diode technology. This technology combines the benefits of excellent low forward voltage and robustness. Consequently, the family is suitable for application requiring high power efficiency

Benefits

- Extremely fast switching
- Low heat dissipation requirements
- Reduce size and cost of the system
- High-reliability
- System efficiency improvement


Applications

- Solar inverter
- Power factor correction
- Data Center
- Switch mode power supply
- AC/DC converters

Features

V_{RRM}	I_F	$T_{J,max}$	Q_C
1200 V	2 A	175 °C	11.2nC

- High surge current capability
- No reverse recovery
- Positive Temperature Coefficient
- Specified dv/dt ruggedness
- Halogen-free / RoHS compliant



Absolute Maximum Ratings ($T_C = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter		Value	Unit
V_{RRM}	Repetitive Peak Reverse Voltage		1200	V
I_F	Forward Current	$T_C = 25^{\circ}C$	9	A
		$T_C = 149^{\circ}C$	5	A
		$T_C = 165^{\circ}C$	2	A
$I_{F,SM}$	Non-Repetitive Forward Surge Current	$T_C = 25^{\circ}C, t_p = 10\text{ ms}$	27	A
		$T_C = 110^{\circ}C, t_p = 10\text{ ms}$	20	A
$I_{F,RM}$	Repetitive Peak Forward Surge Current	$T_C = 25^{\circ}C, t_p = 10\text{ ms}$	16	A
I^2dt value	$\int I^2 dt$	$T_C = 25^{\circ}C, t_p = 10\text{ ms}$	1.62	A ² s
		$T_C = 110^{\circ}C, t_p = 10\text{ ms}$	1.28	A ² s
P_{tot}	Power Dissipation	$T_C = 25^{\circ}C$	55	W
		$T_C = 110^{\circ}C$	24	W
		$T_C = 150^{\circ}C$	9	W
T_J, T_{STG}	Operating Junction and Storage Temperature		-55 to +175	°C

Thermal Characteristics

Symbol	Parameter	Value	Unit
R _{θJC}	Thermal Resistance, Junction to Case, Typ.	2.75	°C/W

Electrical Characteristics (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
V _{DC}	DC blocking voltage		1200	-	-	V
V _F	Forward Voltage	I _F =2A, T _J =25°C	-	1.35	1.80	V
		I _F =2A, T _J =175°C	-	1.8	-	
I _R	Reverse Current	V _R = 1200 V, T _J = 25°C	-	2	20	μA
		V _R = 1200 V, T _J = 175°C	-	40	100	
Q _C	Total Capacitive Charge	V _R = 800 V, T _J = 25°C	-	11.2	-	nC
C	Total capacitance	V _R =0V, f=1MHZ	-	148	-	pF
		V _R =400V, f=1MHZ	-	11	-	pF
		V _R =800V, f=1MHZ	-	8	-	pF
E _C	Capacitance StoredEnergy	V _R =800V	-	5.80	-	uJ

Typical Performance Characteristics

Figure 1. Forward Characteristics




Figure 2. Reverse Characteristics




Figure 3. Peak Forward Current Derating




Figure 4. Power Dissipation




Figure 5. Capacitance vs. Reverse Voltage






Figure 6. Capacitance Charge vs. Reverse Voltage




Typical Performance Characteristics



Package Outlines

TO252NC



COMMON DIMENSIONS

SYMBOL	mm		
	MIN	NOM	MAX
A	2.20	2.30	2.38
A1	0.00	-	0.12
A2	0.97	1.07	1.17
b	0.68	0.78	0.90
b3	5.20	5.33	5.46
c	0.43	0.53	0.61
D	5.98	6.10	6.22
D1	5.30REF		
E	6.40	6.60	6.73
E1	4.63	-	-
e	2.286BSC		
H	9.40	10.10	10.50
L	1.38	1.50	1.75
L1	2.90REF		
L2	0.51BSC		
L3	0.88	-	1.28
L4	0.50	-	1.00
L5	1.65	1.80	1.95
θ	0°	-	8°

* Dimensions in millimeters

Package Marking and Ordering Information

Part Number	Top Marking	Package	Packing Method	Reel Size	Tape Width	Quantity
BCM120S02D3	BCM120S02D3	TO252NC	Tape & Reel	330 mm	16 mm	2500 units

Disclaimer

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co., LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2024 bestirpower – All rights reserved