



1. Configuration & Dimensions: (Unit:mm)



SYMBOL	A	B	C	D	E	F	G	Q'Ty/Disc
ADT120604	14.5Max	14.0Max	9.5Max	4.0±1.0	8.6±0.5	6.3±0.5	0.6±0.1	100

2. Electrical Schematics



Winding order	Origination	Parameter	Requirements
N1,N2	1-2,3-4	2UEW,Φ0.6mm*13.5Ts Ref	--

3. Part Number Code

ADT 120604 Y 112 - GB2
 A B C D E

A: Series Name Power Chokes
 B: Dimensions(mm) 120604: 14.5*14*.95 Max
 C: Tolerance Y: ±40%
 D: Inductance 112=1.1mH
 E: Internal controls

4. Electrical Characteristics

Part Number	Inductance (mH)	Tolerance	Test Frequency (KHz)	DC Resistance (mΩ) Max.
ADT120604Y112-GB2	1.1	±40%	10KHz/0.25V	28.5