

DESCRIPTION

KPESD5V0S1UL a low-capacitance Transient Voltage Suppressor (TVS) designed to provide electrostatic discharge (ESD) protection for high-speed data interfaces. With typical capacitance of 0.4pF, is designed to .

protect parasitic-sensitive systems against over-voltage and over-current transient events. It complies with IEC 61000-4-2 (ESD), Level 4 ($\pm 15\text{kV}$ air, $\pm 8\text{kV}$ contact discharge), IEC 61000-4-4 (electrical fast transient - EFT) (40A, 5/50 ns), very fast charged device model (CDM) ESD and cable discharge event (CDE), etc.


KPESD5V0S1UL ultra-small DFN1006 package.

The K PESD5V0S1UL device can protect one high-speed data line. It offers system designers flexibility to protect single data line where space is a premium concern. The combined features of low capacitance, ultra-small size and high ESD robustness make KPESD5V0S1UL ideal for high-speed data port and high-frequency line applications, such as cellular phones and HD visual devices.

ORDERING INFORMATION

- ◇ **Device:** KPESD5V0S1UL
- ◇ **Package:** DFN1006
- ◇ **Marking:** 5L
- ◇ **Material:** Halogen free
- ◇ **Packing:** Tape & Reel
- ◇ **Quantity per reel:** 10,000pcs

PIN CONFIGURATION



FEATURES

- ◇ Transient protection for high-speed data lines
IEC 61000-4-2 (ESD) $\pm 15\text{kV}$ (Air)
 $\pm 8\text{kV}$ (Contact)
- IEC 61000-4-4 (EFT) 40A (5/50 ns)
Cable Discharge Event (CDE)
- ◇ Package optimized for high-speed lines
- ◇ Ultra-small package (1.0mm×0.6mm×0.5mm)
- ◇ Protects one data, control line
- ◇ Low capacitance: 0.4pF (Typical)
- ◇ Low leakage current
- ◇ Low clamping voltage


MACHANICAL DATA

- ◇ DFN1006 package
- ◇ Flammability Rating: UL 94V-0
- ◇ Packaging: Tape and Reel
- ◇ High temperature soldering guaranteed: $260^{\circ}\text{C}/10\text{s}$
- ◇ Reel size: 7 inch

APPLICATIONS

- ◇ Serial ATA
- ◇ Desktops, Servers and Notebooks
- ◇ Cellular Phones
- ◇ MDDI Ports
- ◇ USB Data Line Protection
- ◇ Display Ports
- ◇ Digital Visual Interfaces (DVI)

CIRCUIT DIAGRAM




ABSOLUTE MAXIMUM RATING


Symbol	Parameter	Value	Units
V_{ESD}	ESD per IEC 61000-4-2 (Air)	± 20	kV
	ESD per IEC 61000-4-2 (Contact)	± 20	
P_{PP}	Peak Pulse Power (8/20 μ s)	60	W
T_{OPT}	Operating Temperature	-55~125	°C
T_{STG}	Storage Temperature	-55~150	°C

ELECTRICAL CHARACTERISTICS (Tamb=25. °C)


Symbol	Parameter	Test Condition	Min	Typ	Max	Units
V_{RWM}	Reverse Working Voltage				5.0	V
V_{BR}	Reverse Breakdown Voltage	$I_R = 1mA$	6.0			V
I_R	Reverse Leakage Current	$V_{RWM} = 5V$			100	nA
V_C	Clamping Voltage	$I_{PP} = 1A, t_p = 8/20\mu s$			10	V
		$I_{PP} = 4A, t_p = 8/20\mu s$			15	V
C_J	Junction Capacitance	$V_R = 0V, f = 1MHz$		0.4	0.5	pF

ELECTRICAL CHARACTERISTICS CURVE


Pulse Waveform




Power Derating Curve

DFN1006 PACKAGE OUTLINE DIMENSIONS


Unit: mm

	MIN	NOM	MAX
D	0.55	0.60	0.65
E	0.95	1.00	1.05
L1	0.20	0.25	0.30
L2	0.20	0.25	0.30
b	0.45	0.50	0.55
e	0.65BSC		
A	0.45	0.50	0.55
h	0.07	0.12	0.17

 Dimension: Millimeter
 (Stencil thickness: 0.1)


Soldering Footprint