

# BCM120S20D2

## Silicon Carbide Schottky Diode

1200 V, 20 A

### Description


BCM120S20D2 utilizes bestirpower's advanced silicon carbide diode technology. This technology combines the benefits of excellent low forward voltage and robustness. Consequently, the family is suitable for application requiring high power efficiency

### Applications

- Solar inverter, UPS
- EV charging station
- Power Factor Correction
- No reverse recovery current
- Low forward voltage
- 175°C Max junction temperature
- High surge current capability
- Switching behavior independent of temperature
- Halogen Free and RoHS compliant

### Features

| $V_{RRM}$ | $I_F$ | $T_C$  | $Q_C$  |
|-----------|-------|--------|--------|
| 1200 V    | 20 A  | 150 °C | 121 nC |



### Absolute Maximum Ratings ( $T_C = 25^{\circ}\text{C}$ unless otherwise noted)

| Symbol         | Parameter                                  |                                                          | Value       | Unit             |
|----------------|--------------------------------------------|----------------------------------------------------------|-------------|------------------|
| $V_{RRM}$      | Repetitive Peak Reverse Voltage            |                                                          | 1200        | V                |
| $I_F$          | Forward Current                            | $T_C = 25^{\circ}\text{C}$                               | 58          | A                |
|                |                                            | $T_C = 135^{\circ}\text{C}$                              | 25          | A                |
|                |                                            | $T_C = 150^{\circ}\text{C}$                              | 20          | A                |
| $I_{F,SM}$     | Non-Repetitive Forward Surge Current       | $T_C = 25^{\circ}\text{C}, t_p = 10\text{ ms}$           | 174         | A                |
|                |                                            | $T_C = 110^{\circ}\text{C}, t_p = 10\text{ ms}$          | 100         | A                |
| $I_{F,Max}$    | Non-Repetitive Peak Forward Current        | $T_C = 25^{\circ}\text{C}, t_p = 10\text{ }\mu\text{s}$  | 1180        | A                |
|                |                                            | $T_C = 150^{\circ}\text{C}, t_p = 10\text{ }\mu\text{s}$ | 980         | A                |
| $I^2dt$ value  | $\int I^2 dt$                              | $T_C = 25^{\circ}\text{C}, t_p = 10\text{ ms}$           | 91          | A <sup>2</sup> s |
|                |                                            | $T_C = 150^{\circ}\text{C}, t_p = 10\text{ ms}$          | 66          | A <sup>2</sup> s |
| $P_{tot}$      | Power Dissipation                          | $T_C = 25^{\circ}\text{C}$                               | 273         | W                |
| $T_J, T_{STG}$ | Operating Junction and Storage Temperature |                                                          | -55 to +175 | °C               |

### Thermal Characteristics

| Symbol          | Parameter                                  | Value | Unit |
|-----------------|--------------------------------------------|-------|------|
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case, Max. | 0.55  | °C/W |

Electrical Characteristics (T<sub>J</sub> = 25°C unless otherwise noted)

| Symbol         | Parameter                 | Test Conditions                                 | Min | Typ  | Max  | Unit |
|----------------|---------------------------|-------------------------------------------------|-----|------|------|------|
| V <sub>F</sub> | Forward Voltage           | I <sub>F</sub> = 20 A, T <sub>J</sub> = 25°C    | -   | 1.39 | 1.70 | V    |
|                |                           | I <sub>F</sub> = 20 A, T <sub>J</sub> = 175°C   | -   | 1.8  | -    |      |
| I <sub>R</sub> | Reverse Current           | V <sub>R</sub> = 1200 V, T <sub>J</sub> = 25°C  | -   | 10   | 100  | µA   |
|                |                           | V <sub>R</sub> = 1200 V, T <sub>J</sub> = 175°C | -   | -    | 300  |      |
| Q <sub>C</sub> | Total Capacitive Charge   | V <sub>R</sub> = 800 V, T <sub>J</sub> = 25°C   | -   | 121  | -    | nC   |
| C              | Total Capacitance         | V <sub>R</sub> = 1 V, f = 100 kHz               | -   | 1357 | -    | pF   |
|                |                           | V <sub>R</sub> = 800 V, f = 100 kHz             | -   | 85   | -    |      |
| E <sub>C</sub> | Capacitance Stored Energy | V <sub>R</sub> = 800 V, T <sub>c</sub> = 25°C   | -   | 34   | -    | µJ   |

Typical Performance Characteristics

Figure 1. Power Derating




Figure 2. Current Derating




Figure 3. Forward Characteristics




Figure 4. Reverse Characteristics




Figure 5. Capacitive Charge Characteristics





Figure 6. Capacitance Stored Energy



Typical Performance Characteristics

Figure 7. Capacitance Characteristics






Figure 8. Transient Thermal Response Curve



Package Outlines

TO252NC



COMMON DIMENSIONS

| SYMBOL | mm       |       |       |
|--------|----------|-------|-------|
|        | MIN      | NOM   | MAX   |
| A      | 2.20     | 2.30  | 2.38  |
| A1     | 0.00     | -     | 0.12  |
| A2     | 0.97     | 1.07  | 1.17  |
| b      | 0.68     | 0.78  | 0.90  |
| b3     | 5.20     | 5.33  | 5.46  |
| c      | 0.43     | 0.53  | 0.61  |
| D      | 5.98     | 6.10  | 6.22  |
| D1     | 5.30REF  |       |       |
| E      | 6.40     | 6.60  | 6.73  |
| E1     | 4.63     | -     | -     |
| e      | 2.286BSC |       |       |
| H      | 9.40     | 10.10 | 10.50 |
| L      | 1.38     | 1.50  | 1.75  |
| L1     | 2.90REF  |       |       |
| L2     | 0.51BSC  |       |       |
| L3     | 0.88     | -     | 1.28  |
| L4     | 0.50     | -     | 1.00  |
| L5     | 1.65     | 1.80  | 1.95  |
| θ      | 0°       | -     | 8°    |

\* Dimensions in millimeters

Package Marking and Ordering Information

| Part Number | Top Marking | Package | Packing Method | Quantity  |
|-------------|-------------|---------|----------------|-----------|
| BCM120S20D2 | BCM120S20D2 | TO252NC | Tape&Reel      | 2500units |

Disclaimer

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co., LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2024 bestirpower – All rights reserved