



FEATURES

- Epitaxial planar die construction.
- Complementary NPN types available(DTC).
- Built-in biasing resistors, $R_1=R_2$.
- Also available in lead free version.




SOT-523



1. IN
2. GND
3. OUT

Equivalent Circuit



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings $T_a = 25^\circ\text{C}$

Symbol	Parameter	Value	Units
V _{CC}	Supply Voltage	50	V
V _{IN}	Input Voltage DTC114EE DTC124EE DTC143EE DTC144EE	-10 to +40 -10 to +40 -10 to +30 -10 to +40	V
I _O	Output Current DTC114EE DTC124EE DTC143EE DTC144EE	50 30 100 30	mA
I _C (Max.)	Output current ALL	100	mA
P _D	Power Dissipation	150	mW
R _{θJA}	Thermal Resistance, Junction to Ambient Air	833	°C/W
T _J , T _{stg}	Operating and Storage and Temperature Range	-55 to +150	°C

ELECTRICAL CHARACTERISTICS (TA = 25°C unless otherwise noted.)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Input Voltage	$V_{I(off)}$	$V_{CC}=5V, I_O=100\mu A$	0.5	1.1	-	V
Input Voltage	$V_{I(on)}$	$V_O=0.3V, I_O=10mA$ $V_O=0.2V, I_O=5mA$ $V_O=0.3V, I_O=20mA$ $V_O=0.3V, I_O=2mA$	-	1.9	3	
Output Voltage	$V_{O(on)}$	$I_O/I_I=10mA/0.5mA,$	-	0.1	0.3	V
Input Current	I_I	$V_I=5V$	-	-	0.88 0.36 1.8 0.18	
Output Current	$I_{O(off)}$	$V_{CC}=50V, V_I=0V$	-	-	0.5	μA
DC Current Gain	G_I	$V_O=5V, I_O=5mA$ $V_O=5V, I_O=5mA$ $V_O=5V, I_O=10mA$ $V_O=5V, I_O=5mA$	30 56 20 68	-	-	k Ω
Input Resistor	$R_1(R_2)$		7 15.4 3.29 32.9	10 22 4.7 47	13 28.6 6.11 61.1	
Resistance Ratio	R_2/R_1	-	0.8	1	1.2	
Gain-Bandwidth Product	f_T	$V_{CE}=10V, I_E=-5mA,$ $f=100MHz$	-	250	-	MHz

RATING AND CHARACTERISTIC CURVES




Fig.1 Input voltage vs. output current
(ON characteristics)




Fig.2 Output current vs. input voltage
(OFF characteristics)





Fig.3 DC current gain vs. output
current

Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150 °C
	-Temperature Max($T_{s(max)}$)	+200 °C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3 °C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3 °C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217 °C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5) °C
Time within 5 °C of actual Peak Temp (t_P)		30 secs. Max
Ramp-down Rate		6 °C/sec. Max
Time 25 °C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260 °C




Package Dimensions & Suggested Pad Layout

SOT-523

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.700	0.900	0.028	0.035
A1	0.000	0.100	0.000	0.004
A2	0.700	0.800	0.028	0.031
b1	0.150	0.250	0.006	0.010
b2	0.250	0.350	0.010	0.014
c	0.100	0.200	0.004	0.008
D	1.500	1.700	0.059	0.067
E	0.700	0.900	0.028	0.035
E1	1.450	1.750	0.057	0.069
e	0.500 TYP.		0.020 TYP.	
e1	0.900	1.100	0.035	0.043
L	0.400 REF.		0.016 REF.	
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°


Dimensions in inches and (millimeters)



Dimensions	Value (in mm)
C	1.00
G	0.45
X	0.70
X1	1.40
X2	0.70
Y	0.60


Tape & reel specification

Tape



Symbol	Dimension (mm)
P0	4.00±0.20
P1	4.00±0.20
P2	2.00±0.20
D0	1.55±0.20
D1	0.65±0.20
E	1.55±0.25
F	3.60±0.20
W	8.00±0.20
A0	2.10±0.20
B0	2.20±0.20
K0	1.10±0.20
T	0.20±0.20
D2	177.0±5.0
D3	55Min.
D4	R24.6±2.0
G	R82.0±2.0
I	13.0±2.0
W1	10.20±3.0

7" Reel



Quantity: 3000PCS