


FEATURES


- Fast switching speed.
- For general purpose switching applications.
- High conductance.

V_R 100 V
 I_D 0.2 A


SOT-23




MMBD4148:KA2




MMBD4148CA:D6



MMBD4148CC:D5



MMBD4148SE:D4



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Maximum Ratings @Ta=25°C

Parameter	Symbol	Value	Unit
Non-Repetitive Peak Reverse Voltage	V_{RM}	100	V
Peak Repetitive Peak Reverse Voltage	V_{RRM}	100	V
Working Peak Reverse Voltage	V_{RWM}		
DC Blocking Voltage	V_R		
RMS Reverse Voltage	$V_{R(RMS)}$	75	V
Forward Continuous Current	I_{FM}	300	mA
Average Rectified Output Current	I_o	200	mA
Peak Forward Surge Current @t=1.0μs @ t=1.0s	I_{FSM}	2.0 1.0	A
Power Dissipation	P_D	350	mW
Thermal Resistance Junction to Ambient	R_{thJA}	357	°C/W
Junction Temperature	T_J	150	°C
Storage Temperature	T_{STG}	-55 ~ +150	°C

Electrical Characteristics@Ta=25°C

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Reverse breakdown voltage	$V_{(BR)1}$	$I_R=100\mu A$	100			V
	$V_{(BR)2}$	$I_R=5\mu A$	75			V
Forward voltage	V_F	$I_F=10mA$			1.0	V
Reverse current	I_{R1}	$V_R=75V$			5.0	μA
	I_{R2}	$V_R=25V$			25	nA
Capacitance between terminals	C_T	$V_R=0V, f=1MHz$			4.0	pF
Reverse recovery time	t_{rr}	$I_F=I_R=10mA, V_R=6V$ $I_{rr}=0.1 \times I_R, R_L=100\Omega$			4.0	ns

RATING AND CHARACTERISTIC CURVES

Fig.1 Power Derating Curve




Fig.2 Reverse Characteristics




Fig.3 Forward Characteristics






Fig.4 Capacitance Characteristics





Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150 °C
	-Temperature Max($T_{s(max)}$)	+200 °C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3 °C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3 °C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217 °C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5) °C
Time within 5 °C of actual Peak Temp (t_P)		30 secs. Max
Ramp-down Rate		6 °C/sec. Max
Time 25 °C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260 °C



Package Dimensions & Suggested Pad Layout

SOT23





SOT-23 mechanical data

UNIT		A	C	D	E	H _E	e	M	L	L ₁	a
mm	max	1.1	0.15	1.4	3.0	2.6	0.5	1.95	0.55 (ref)	0.36 (ref)	0.0
	min	0.9	0.08	1.2	2.8	2.2	0.3	1.7			0.15
mil	max	43	6	55	118	102	20	77	22 (ref)	14 (ref)	0.0
	min	35	3	47	110	87	12	67			6

Dimensions	SOT23
Z	2.9
X	0.8
Y	0.9
C	2.0
E	1.35

Tape & reel specification

Tape		Symbol	Dimension (mm)
		P0	4.00±0.10
		P1	4.00±0.10
		P2	2.00±0.10
		D0	1.55±0.10
		D1	1.05±0.10
		E	1.55±0.10
		F	3.60±0.10
		W	8.00±0.10
		A0	3.80±0.20
		B0	3.25±0.20
		K0	1.45±0.10
		T	0.25±0.05
		D2	178.0±3.0
7" Reel		D3	55Min.
		D4	R24.0±3.0
		G	R82.0±3.0
		I	13.0±2.0
		W1	11.0±3.0
		Quantity: 3000PCS	