



Technical Requirements:

- 1,100% continuity testing shall be performed on finished products: no short circuit, open circuit or misconnection is allowed.
- 2,Continuity resistance: 2Ω MAX
- 3,Insulation resistance: 10Ω MIN
- 4,Test voltage: 300VDC
- 5,Products comply with ROHS + REACH standards.

P2
Plating Sn

P1
XHB2. 54-2Y

3.0±0.3mm Plating Sn P1 Red

3.0±0.3mm Plating Sn P2 Black

Part		XHB2.54-2Y/ Plating Sn UL1007-24# L=200mm					
6							
5							
4							
3	Terminal	XHB2.54 Plating Sn				2	pcs
2	Housing	XHB2.54-2Y				1	pcs
1	Wire	UL1007-24AWG R/B wire L=200mm,end plating Sn 3mm	103mm	1.0/3.0T		2	pcs
No.	Material	Description	Cut length of the wires	Set wire stripping length	wire length	QTY	Unit

贝迅泽 BEIXUNZE 贝迅泽技术（东莞）有限公司 BEIXUNZE TECHNOLOGY (DONGGUAN) CO., LTD				
www.hiemi.cn		PN:	XHB2.54-2P-A-200-24A	
Drawn	CHC	Date	2024-11-19	A0
Check	LIKE	Date	2024-11-19	
Approved	WSR	Date	2024-11-19	