

1000BASE-TX TRANSFORMER MODULES



Features:


- Designed to meet IEEE 802.3 requirements.
- Peak solder temperature rating per Table 5-2 in IPC/JEDEC J-STD-020C
- IEEE 802.3 AT/ANSI X3.263 compliant performance.
- RoHS compliant

Specifications:


- Primary inductance (LP):350uH,min.@100KHz,0.1Vrms,18mA .

Electrical Specification@25℃ Operating Temperature -40 to + 85℃														
Part No.	Insertion loss (dB MAX) 1-100MHz	Return loss (dB MHz)					Differential to COMMON Mode Rejection (dB MIN)			Crosstalk (dB MIN .) MHz				Hipot (Vrms MIN)
		1-30MHz	40MHz	50MHz	60-80MHz	100MHz	30MHz	60MHz	100MHz	30MHz	60MHz	100MHz		
UKGP4805SR	-1.0	-16	-14.4	-13.1	-12	-10	-45	-40	-35	-43.5	-37.5	-33	1500	

Dimension:mm(inch)+/-0.25(0.01)




Schematic



5.SUGGEST PROFILE

IR reflow graph



IR reflow profile

Form-1 (Reference JEDEC J-STD-020C Table 5-2))

IR reflow profile		Sn-Pb	Pb-free
step#	Profile Feature	Condition/Duration	Condition/Duration
step1	Ramp-up rate	1.5-3°C/sec.	1.5-3°C/sec.
step2	Preheat : 100~150°C(Ta-Tb)	t1-t2 : 60~120 sec.	t1-t2 : 60~180 sec.
step3	Ramp-up rate(T _L to T _P)	1.5-3°C/sec.	1.5-3°C/sec.
	Temperature maintained above 183°C(T _L)	T _L : 60-150sec.	T _L : 80-150sec.
step4	Peak temperature(T _P)	230+5/-10°C	260+0/-5°C
	Time within 5°C of actual peak temperature	30±10 sec.	30±10 sec.
step5	Ramp-down rate	6°C/sec.Max	6°C/sec.Max
Note1	Subject the samples to 3 cycles of the above defined reflow conditions		Subject the samples to 3 cycles of the above defined reflow conditions
Note2	Time 25°C to peak temperature : 6 minutes max.		Time 25°C to peak temperature : 8 minutes max.
Note3			The time between reflows shall be 5 minutes minimum and 60minutes maximum

SnPb Eutectic Process- “Package Peak Reflow Temperature”

Form-2 (Reference JEDEC J-STD-020C Table 4-1)

产品厚度	产品体积<350mm ³	产品体积≥350mm ³
<2.5mm	240 +0/-5°C	225 +0/-5°C
≥2.5mm	225 +0/-5°C	225 +0/-5°C

Pb-free Process - “Package Peak Reflow Temperature”

Form-3 (Reference JEDEC J-STD-020C Table 4-2)

产品厚度	产品体积<350mm ³	产品体积 350mm ³ -2000mm ³	产品体积>2000mm ³
<1.6mm	260 +0/-5°C	260 +0/-5°C	260 +0/-5°C
1.6mm-2.5mm	260 +0/-5°C	250 +0/-5°C	245 +0/-5°C
>2.5mm	250 +0/-5°C	245 +0/-5°C	245 +0/-5°C



Dongguan Usakro Electronic Technology Co., Ltd.

REV: 00


东莞市美韩电子科技有限公司

Page: 3 of 5


6. Reliability

No.	Test Item	Refer To Standard	Test Condition
1	Resistance To Soldering Heat--Convection Reflow	IPC/JEDEC J-STD-020D	1).Peak Temperature: Refer to Specification According to Package Body Thickness And Volume 2).Preheat Temperature and Soak Time: 150~200℃,60~120 Seconds 3).Average Ramp-up Rate: 3℃/Second Max 4).Above 217℃: 60~150 Seconds 5).Peak Temperature-5℃: Over 30 S
2	Thermal Shock	IEC68-2-14 Method A	1.Low Temperature:-40℃ 2.High Temperature:125 3.Dwell Time:30 Minutes 4.Transition Time: Less Than 5Minutes 5.Number of Cycles: 10
3	High Temperature	IEC68-2-2 Method A	125℃,96Hours
4	Low Temperature	IEC68-2-1 Method A	-40℃,96Hours
5	Temperature Humidity Cycle	IEC68-2-38	Temp Humidity soak time 25~65℃ 93+/-3%RH 1.5 hr 65℃ 93+/-3%RH 4 hr 65~25℃ 80~96%RH 2.5 hr 25~65℃ 93+/-3%RH 1.5hr 65℃ 93+/-3%RH 4hr 65~25℃ 80~96%RH 2
6	Vibration	IEC68-2-6	1.Sine Wave 2.Amplitude:0.75mm 3.Frequence:5~500~5Hz 4.Direction: X,Y,Z 5.Number of Sweep Cycles Per Direction:10 6.Duration: 2 Hours Each Direction
7	Mechanical Shock	MIL-STD-202	1).Half -Sine Wave 2).Peak Acceleration:50G 3).Duration:11mS 4).Direction: X,Y,Z,-X,-Y,-Z 5).Number of Shock Per Direction:3
8	Free Drop	ISO4180	1) Height: Refer to Specification According to Production weight 2).1Corner,3Edges,6Faces .Total Are 10 Times
9	Solderability	JESD22-B102D	1).Precondition:150±5℃,16±0.5Hours 2).Flux Type:ROL1 3).Immersion Flux Time: 5~10 Seconds 4).Solder Temperature:245±5℃ 5).Solder Immersion Time:5±0.5 Seconds 6).Solder Immersion/Emersion Speed:25.4±6.4mm/Second
10	Accelerated Moisture Resistance---Unbiased Autoclave	JESD22-A102-C	1.Temperature:121℃ 2. Humidity: 100% 3. Vapor Pressure: 29.7 Psia or 205KPa 4.Duration:96 hours

7 CARRIER TAPE



8 PACKAGE



Product	PCS/Reel	PCS/Box	Product No.	Weigh(g/pcs)
SMD 48PIN Series	350	350x4=1400	UKGP4805SR	2.8