


GVZ 105°C, Lower Impedance. Series



Features


105°C, 2000~3000 hours assured, Extra low Impedance.
Impedance 50~70% less than GVE series.
Available for high density surface mounting.



Specifications

Item	Condition		Specifications							
Category Temperature Range(°C)	—		-55°C ~ +105°C							
Capacitance Tolerance (%)	120Hz, 20°C		±20%							
Rated Voltage (V)	—		6.3	10	16	25	35	50	63	100
Dissipation Factor (tanδ)	120Hz, 20°C (Max.)	tanδ	0.26	0.18	0.16	0.14	0.12	0.10	0.10	0.07
		Notes	Exceeding 1,000uF, +0.02 every 1,000uF							
Leakage Current (LC)	After 2 minutes, 20°C (uA, Max.)		0.01CV or 3uA, whichever is greater.							
Low Temperature Characteristics	Impedance Ratio (Max.)	Z _{-25°C} /Z _{+20°C}	4	3	2	2	2	2	2	2
		Z _{-55°C} /Z _{+20°C}	8	5	4	3	3	3	3	3
Endurance	105°C, Rated Voltage Applied (With the rated ripple current)	Hours	3,000 (2,000hrs. for Ø4~Ø6.3)							
		ΔC/C	Within ±30% of initial value							
		tanδ	300% or less of the initial specified value							
		LC	The initial specified value or less							
Shelf life	105°C	Hours	1,000							
		Other Items	same as those for the endurance.							

Dimensions



D	L	A	B	C	P	α	W
4	5.7	4.3	4.3	5.0	1.0	±0.3	0.5-0.8
5	5.7	5.3	5.3	6.0	1.5	±0.3	0.5-0.8
6.3	5.7	6.6	6.6	7.3	2.0	±0.3	0.5-0.8
6.3	7.7	6.6	6.6	7.3	2.0	±0.3	0.5-0.8
8	10.5	8.3	8.3	9.0	3.1	±0.5	0.7-1.2
10	10.5	10.3	10.3	11.0	4.7	±0.5	0.7-1.2

Rated Ripple Current Multipliers

Frequency (Hz) Capacitance (uF)	50	120	1k	10k	100K
Under 100	0.35	0.50	0.70	0.90	1.00
100 ~ 2200uF	0.40	0.65	0.85	0.95	1.00

GVZ

Series

■ Dimensions

uF	WV	6.3v			10v			16v			25v			35v			50v		
		$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.
1																	4x5.7	2.9	60
1.5																	4x5.7	2.9	60
2.2																	4x5.7	2.9	60
3.3														4x5.7	1.8	80	4x5.7 5x5.7	2.9 1.52	60 85
4.7														4x5.7	1.8	80	4x5.7 5x5.7	2.9 1.52	60 85
10											4x5.7	1.8	80	4x5.7 5x5.7	1.8 0.76	80 150	5x5.7 6.3x5.7	1.52 0.88	85 165
15								4x5.7	1.8	80	4x5.7	1.8	80	5x5.7	0.76	150	6.3x5.7	0.88	165
22					4x5.7	1.8	80	4x5.7 5x5.7	1.8 0.76	80 150	4x5.7 5x5.7	1.8 0.76	80 150	5x5.7	0.76	150	6.3x5.7	0.88	165
33					4x5.7	1.8	80	4x5.7 5x5.7	1.8 0.76	80 150	4x5.7 5x5.7	1.8 0.76	80 150	5x5.7 6.3x5.7	0.76 0.44	150 230	6.3x5.7 6.3x7.7	0.88 0.68	165 185
47		4x5.7	1.8	80	4x5.7 5x5.7	1.8 0.76	80 150	5x5.7 6.3x5.7	0.76 0.44	150 230	5x5.7 6.3x5.7	0.76 0.44	150 230	6.3x5.7	0.44	230	6.3x5.7 6.3x7.7	0.88 0.68	165 185
56		5x5.7	0.76	150	4x5.7 5x5.7	1.8 0.76	80 150	5x5.7 6.3x5.7	0.76 0.44	150 230	6.3x5.7	0.44	230	6.3x5.7	0.44	230	6.3x7.7	0.68	185
68		5x5.7	0.76	150	5x5.7	0.76	150	5x5.7 6.3x5.7	0.76 0.44	150 230	6.3x5.7	0.44	230	6.3x5.7 6.3x7.7	0.44 0.34	230 280	6.3x7.7	0.68	185
100		5x5.7	0.76	150	5x5.7 6.3x5.7	0.76 0.44	150 230	5x5.7 6.3x5.7	0.76 0.44	150 230	6.3x5.7 6.3x7.7	0.44 0.34	230 280	6.3x5.7 6.3x7.7	0.44 0.34	230 280	6.3x7.7 8x10.5	0.68 0.34	185 350
150		5x5.7 6.3x5.7	0.76 0.44	150 230	6.3x5.7	0.44	230	6.3x5.7 6.3x7.7	0.44 0.34	230 280	6.3x7.7 8x10.5	0.34 0.17	280 600	6.3x7.7 8x10.5	0.34 0.17	280 600	10x10.5	0.18	670
220		6.3x5.7	0.44	230	6.3x5.7 6.3x7.7	0.44 0.34	230 280	6.3x5.7 6.3x7.7	0.44 0.34	230 280	8x10.5	0.17	600	8x10.5 10x10.5	0.17 0.09	600 820	10x10.5	0.18	670
330		6.3x5.7 6.3x7.7	0.44 0.34	230 280	6.3x7.7	0.34	280	6.3x7.7 8x10.5	0.34 0.17	280 600	8x10.5 10x10.5	0.17 0.09	600 820	10x10.5	0.09	820	10x10.5 10x12.5	0.18 0.16	670 720
470		6.3x7.7	0.34	280	6.3x7.7 8x10.5	0.34 0.17	280 600	8x10.5	0.17	600	10x10.5 10x12.5	0.09 0.075	820 820	10x10.5 10x12.5	0.09 0.075	820 820			
680		8x10.5	0.17	600	8x10.5	0.17	600	8x10.5 10x10.5	0.17 0.09	600 820									
1000		8x10.5	0.17	600	8x10.5 10x10.5	0.17 0.09	600 820	10x10.5	0.09	820									
1500		8x10.5 10x10.5	0.17 0.09	600 820															

Note1: Case size $\Phi D \times L$ (mm), ripple current (mA, rms) at 105°C, 100KHz.

Note2: Produce custom product too, which are not found in these tables.

GVZ Series


■ Dimensions

uF	WV	63v			80v			100v		
		$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.
4.7		5x5.7	1.9	70						
10		5x5.7 6.3x5.7	1.9 1.2	70 130	6.3x5.7 6.3x7.7	2.4 1.8	65 75	6.3x7.7	1.8	75
22		6.3x5.7 6.3x7.7	1.2 0.9	130 150	6.3x7.7 8x10.5	1.8 1.3	75 130	8x10.5	1.3	130
33		6.3x7.7 8x10.5	0.9 0.5	150 280	8x10.5	1.3	130	8x10.5 10x10.5	1.3 0.7	130 200
47		8x10.5	0.50	280	8x10.5	1.3	130	10x10.5	0.7	200
56		8x10.5	0.50	280	8x10.5	1.3	130	10x10.5	0.7	200
68		8x10.5	0.50	280	10x10.5	0.7	200	10x10.5	0.7	200
82		8x10.5 10x10.5	0.50 0.25	280 450	10x10.5	0.7	200			
100		10x10.5	0.25	450	10x10.5	0.7	200			
150		10x10.5	0.25	450						

Note1: Case size $\Phi D \times L$ (mm), ripple current (mA, rms) at 105°C, 120Hz.

Note2: Produce custom product too, which are not found in these tables.

■ 编码规则表



Brand	Series	Voltage (W.V)	Code	Capacitance (UF)	Code	Size φDxL	Code
RY	GVS	4	4V	0.1	0.1UF	4 × 5(5.7)	4*5
	GVT	6.3	6.3V	0.22	0.22UF	4 × 7	4*7
	GVE	10	10V	0.33	0.33UF	5 × 5(5.7)	5*5
	GVZ	16	16V	0.47	0.47UF	5 × 7	5*7
	GVM	25	25V	1	1UF	5 × 11	5*11
	GVL	35	35V	2.2	2.2UF	6.3 × 5(5.7)	6*5
	GVU	50	50V	3.3	3.3UF	6.3 × 7(7.7)	6*7
	GVY	63	63V	4.7	4.7UF	6.3 × 11	6*11
	GVF	80	80V	10	10UF	8 × 5	8*5
	GVR	100	100V	22	22UF	8 × 6.5	8*6
	GVG	125	125V	33	33UF	8 × 9	8*9
	GVD	160	160V	47	47UF	8 × 10(10.5)	8*10
	GVP	180	180V	68	68UF	8 × 11(11.5)	8*11
	GVT	200	200V	100	100UF	8 × 12	8*12
	GVC	220	220V	220	220UF	10 × 10(10.5)	10*10
	GVN	250	250V	330	330UF	10 × 12.5	10*12
	GVK	315	315V	470	470UF	10 × 14	10*14
	GVA	330	330V	680	680UF	12.5 × 13.5	12*13
		350	350V	1000	1000UF	12.5 × 16	12*16
		400	400V	2200	2200UF	16 × 16.5	16*16
		420	420V	3300	3300UF	16 × 25	16*25
		450	450V	4700	4700UF	20 × 25	20*25
		500	500V	6800	6800UF	35 × 42	35*42

Taping Specifications

Carrier Tape

Fig.01




Fig.02






Fig.03



Case Size	W (mm)	W1 (mm)	F (mm)	P (mm)	P1 (mm)	P2 (mm)	A (mm)	B (mm)	t1 (mm)	t2 (mm)
$\phi 4 \times 5.7$	12	1.75	5.5	8	2	4	4.7	4.7	0.4	6.3
$\phi 5 \times 5.7$	12		5.5	12			6	6		6.3
$\phi 6.3 \times 4.5$	16		7.5	12			7	7		4.8
$\phi 6.3 \times 5.2 \sim 5.7$	16		7.5	12			7	7		6.3
$\phi 6.3 \times 7.0$	16		7.5	12			7	7		6.8
$\phi 6.3 \times 7.7$	16		7.5	12			7	7		8.3
$\phi 6.3 \times 8.7$	16		7.5	12			7	7	0.5	9.3
$\phi 8 \times 10.5$	24		11.5	16			8.7	8.7		11.0
$\phi 10 \times 10.5$	24		11.5	16			10.7	10.7		11.0
$\phi 10 \times 12.5$	24		11.5	16			10.7	10.7		13.1
$\phi 12.5 \times 13.5$	32		14.2	24			14	14		14.5
$\phi 12.5 \times 16$	32		14.2	24			14	14		17.0
$\phi 16 \times 16.5$	44	1.75	20.2	28	2	4	17.5	17.5	0.5	17.5
$\phi 16 \times 21.5$	44		20.2	28			17.5	17.5		23.0
Tolerance	± 0.3	± 0.15	± 0.1	± 0.1	± 0.1	± 0.1	± 0.2	± 0.2	± 0.1	± 0.2

Reel & Package Quantity




Case Size	Reel	Carton	A ± 0.3	B ± 2	Case Size	Reel	Carton	A ± 0.3	B ± 2
$\phi 4 \times 5.7$	2000	20000	14	382	$\phi 8 \times 10.5$	500	5000	26	382
$\phi 5 \times 5.7$	1250	12500	14	382	$\phi 8 \times 12.5$	500	5000	26	382
$\phi 6.3 \times 4.5$	1500	15000	18	382	$\phi 10 \times 10.5$	500	5000	26	382
$\phi 6.3 \times 5.2$	1250	12500	18	382	$\phi 10 \times 12.5$	500	5000	26	382
$\phi 6.3 \times 5.7$	1250	12500	18	382	$\phi 12.5 \times 13.5$	250	750	34	332
$\phi 6.3 \times 7.0$	1000	10000	18	382	$\phi 12.5 \times 16.5$	200	600	34	332
$\phi 6.3 \times 7.7$	1000	10000	18	382	$\phi 16 \times 16.5$	200	600	34	332
$\phi 6.3 \times 8.7$	700	7000	18	382	$\phi 16 \times 21.5$	200	600	34	332

Reflow Soldering Conditions

Recommended soldering heat conditions

1. The following conditions are recommended for air convection and infrared reflow soldering on the SMD products onto a glass epoxy circuit boards by cream solder. The temperatures shown are the surface temperature values on the top of the can and on the capacitor terminals.
2. Reflow should be performed twice or less.
3. Please ensure that the capacitor became cold enough to the room temperature (5 to 35°C) before the second reflow.

Classification Reflow Profile




Notice:

1. Average ramp-up rate is 5°C/second max.
2. Ramp-down rate is 6°C/second max.
3. Time from 25°C to peak temperature is 6 minutes max.

	Preheat	Time maintained above 200°C	Time maintained above 220°C	Time maintained above 230°C	Peak temp.	Reflow number
Dia. 4~10mm general	120°C to 180°C 120 sec. Max.	60 sec.	50 sec.	30 sec.	250°C Max.	2 times or less
φ8x6.5		50 sec.	40 sec.	25 sec.	245°C Max.	2 times or less
WV 160v-450v		60 sec.	50 sec.	30 sec.	240°C Max.	2 times or less
Dia. 12.5~20mm Cap.		60 sec.	40 sec.	30 sec.	240°C Max.	2 times or less
125°C Category Temp.		60 sec.	40 sec.	30 sec.	250°C Max.	2 times or less

Recommended Solder Land Size on PC Board



Size	X	Y	a
φ4	1.6	2.6	1.0
φ5	1.6	3.0	1.4
φ6.3	1.6	3.5	2.1
φ8x6.5	1.6	4.5	2.1
φ8x10.5	2.5	3.5	3.0
φ10	2.5	4.0	4.0
φ12.5	3.0	5.7	4.0
φ16	3.5	6.5	6.0

■ Correspondence to Environment

We always considers the environment in product materials, designs and manufacturing. Cadmium, Mercury, Hexavalent Chromium, PBB and PBDE have never been used in our products. Furthermore, lead-containing materials have been eliminated from all our aluminum electrolytic capacitors including Conductive Polymer Aluminum Solid Capacitors to comply with RoHS. If you need "Halogen-Free" products, please consult with us.

① RoHS Compliance RoHS

All capacitors comply with RoHS directive (2011/65/EU)

Lead (Pb)	≤1,000ppm
Mercury (Hg)	≤1,000ppm
Cadmium (Cd)	≤100ppm
Hexavalent Chromium (Cr ⁶⁺)	≤1,000ppm
Polybrominated Biphenyls (PBBs)	≤1,000ppm
Polybrominated Diphenyl Ethers (PBDEs)	≤1,000ppm

② Lead-free Compliance

All complete parts and homogenous materials of capacitors are lead-free.

③ Halogen-free Compliance

The products identified in the catalogue, and their homogeneous subcomponents, do not contain any of the following substances in concentrations greater than the listed maximum limits.

The content percentage of chlorine (Cl)	≤900ppm
The content percentage of bromine (Br)	≤900ppm
The content percentage of chlorine (Cd) and bromine (Br) (Cl+Br)	≤1,500ppm

④ Regarding compliance for EU REACH Regulation

1). According to the content of REACH handbook (Guidance on requirements for substances in articles which is published on May 2008), our electronic components are "articles without any intended release". Therefore they are not applicable for "Registration" for EU REACH Regulation Article 7 (1).

Reference: Electrolytic Condenser Investigation Society "Study of REACH Regulation in EU about Electrolytic Capacitor" (publicized on 13 March 2008)

2). We develops the products without substance of very high concern (SVHC- Substances of Very High Concern).

⑤ Non-PVC Products

Category		Sleeve Material
Conductive polymer Aluminum Solid Capacitors	Chip	Sleeveless
	Radial	Sleeveless
Aluminum Electrolytic Capacitors	Chip	Sleeveless
	Radial	PVC or PET
	Snap-in	
	Screw Mount	PVC

※: Identification of friendly parts is given by a sleeve code (14th digit) of the part number. For details, please refer to "Product code guide" for each type.