

GVE 105°C, Low Impedance.
Series



Features

105°C, 2000~3000 hours assured, Low Impedance.


Available for high density surface mounting.

High stability and reliability.

Specifications

Item	Condition		Specifications							
Category Temperature Range(°C)	—		-55°C ~ +105°C							
Capacitance Tolerance (%)	120Hz, 20°C		±20%							
Rated Voltage (V)	—		6.3	10	16	25	35	50	63	100
Dissipation Factor (tanδ)	120Hz, 20°C (Max.)	tanδ	0.26	0.20	0.16	0.14	0.12	0.12	0.12	0.08
		Notes	Exceeding 1,000uF, +0.02 every 1,000uF							
Leakage Current (LC)	After 2 minutes, 20°C (uA, Max.)		0.01CV or 3uA, whichever is greater.							
Low Temperature Characteristics	Impedance Ratio (Max.)	Z _{-25°C} /Z _{+20°C}	4	3	2	2	2	2	2	2
		Z _{-55°C} /Z _{+20°C}	8	5	4	3	3	3	3	3
Endurance	105°C, Rated Voltage Applied (With the rated ripple current)	Hours	3,000 (2,000hrs. for Ø4~Ø6.3)							
		ΔC/C	Within ±30% of initial value							
		tanδ	300% or less of the initial specified value							
		LC	The initial specified value or less							
Shelf life	105°C	Hours	1,000							
		Other Items	same as those for the endurance.							

Dimensions



D	L	A	B	C	P	α	W
4	5.7	4.3	4.3	5.0	1.0	±0.3	0.5-0.8
5	5.7	5.3	5.3	6.0	1.5	±0.3	0.5-0.8
6.3	5.7	6.6	6.6	7.3	2.0	±0.3	0.5-0.8
6.3	7.7	6.6	6.6	7.3	2.0	±0.3	0.5-0.8
8	10.5	8.3	8.3	9.0	3.1	±0.5	0.7-1.2
10	10.5	10.3	10.3	11.0	4.7	±0.5	0.7-1.2

Rated Ripple Current Multipliers

Frequency (Hz) Capacitance (uF)	50	120	1k	10k	100K
Under 100	0.35	0.50	0.70	0.90	1.00
100 ~ 2200uF	0.40	0.65	0.85	0.95	1.00

GVE Series

■ Dimensions

uF	WV	6.3v(0J)			10v(1A)			16v(1C)			25v(1E)			35v(1V)			50v(1H)		
		$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.
1																	4x5.7	5.0	30
1.5																	4x5.7	5.0	30
2.2																	4x5.7	5.0	30
3.3														4x5.7	3.0	60	4x5.7 5x5.7	5.0 3.0	30 50
4.7														4x5.7	3.0	60	4x5.7 5x5.7	5.0 3.0	30 50
10											4x5.7	3.0	60	4x5.7 5x5.7	3.0 1.8	60 95	5x5.7 6.3x5.7	3.0 2.0	50 70
15								4x5.7	3.0	60	4x5.7	3.0	60	5x5.7	1.8	95	6.3x5.7	2.0	70
22					4x5.7	3.0	60	4x5.7 5x5.7	3.0 1.8	60 95	4x5.7 5x5.7	3.0 1.8	60 95	5x5.7	1.8	95	6.3x5.7	2.0	70
33					4x5.7	3.0	60	4x5.7 5x5.7	3.0 1.8	60 95	4x5.7 5x5.7	3.0 1.8	60 95	5x5.7 6.3x5.7	1.8 1.0	95 140	6.3x5.7 6.3x7.7	2.0 1.0	70 120
47		4x5.7	3.0	60	4x5.7 5x5.7	3.0 1.8	60 95	5x5.7 6.3x5.7	1.8 1.0	95 140	5x5.7 6.3x5.7	1.8 1.0	95 140	6.3x5.7	1.0	140	6.3x7.7	1.0	120
56		5x5.7	1.8	95	4x5.7 5x5.7	3.0 1.8	60 95	5x5.7 6.3x5.7	1.8 1.0	95 140	6.3x5.7	1.0	140	6.3x5.7	1.0	140	6.3x7.7	1.0	120
68		5x5.7	1.8	95	5x5.7	1.8	95	5x5.7 6.3x5.7	1.8 1.0	95 140	6.3x5.7	1.0	140	6.3x5.7 6.3x7.7	1.0 0.6	140 230	6.3x7.7 8x10.5	1.0 0.6	120 300
100		5x5.7	1.8	95	5x5.7 6.3x5.7	1.8 1.0	95 140	6.3x5.7 6.3x7.7	1.0 0.6	140 230	6.3x5.7 6.3x7.7	1.0 0.6	140 230	6.3x7.7	0.6	230	8x10.5 10x10.5	0.6 0.3	300 500
150		5x5.7 6.3x5.7	1.8 1.0	95 140	6.3x5.7	1.0	140	6.3x5.7 6.3x7.7	1.0 0.6	140 230	6.3x7.7 8x10.5	0.6 0.3	230 450	6.3x7.7 8x10.5	0.6 0.3	230 450	10x10.5	0.3	500
220		6.3x5.7	1.0	140	6.3x5.7 6.3x7.7	1.0 0.6	140 230	6.3x7.7	0.6	230	8x10.5	0.3	450	8x10.5 10x10.5	0.3 0.15	450 670	10x10.5 10x12.5	0.3 0.16	500 580
330		6.3x5.7 6.3x7.7	1.0 0.6	140 230	6.3x7.7	0.6	230	6.3x7.7 8x10.5	0.6 0.3	230 450	8x10.5 10x10.5	0.3 0.15	450 670	10x10.5	0.15	670			
470		6.3x7.7	0.6	230	6.3x7.7 8x10.5	0.6 0.3	230 450	8x10.5	0.3	450	10x10.5 10x12.5	0.15 0.075	670 800	10x10.5 10x12.5	0.15 0.075	670 800			
680		8x10.5	0.3	450	8x10.5	0.3	450	8x10.5 10x10.5	0.3 0.15	450 670									
1000		8x10.5	0.3	450	8x10.5 10x10.5	0.3 0.15	450 670	10x10.5	0.15	670									
1500		8x10.5 10x10.5	0.3 0.15	450 670															

Note1: Case size $\Phi D \times L$ (mm), ripple current (mA, rms) at 105°C, 100KHz.

Note2: Produce custom product too, which are not found in these tables.

GVE

Series


■ Dimensions

uF \ WV	63v(1J)			80v(1K)			100v(2A)		
	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.	$\Phi D \times L$	Imp.	R.C.
4.7	5x5.7	3.0	50						
10	5x5.7 6.3x5.7	3.0 1.5	50 80	6.3x5.7 6.3x7.7	3.0 2.4	40 60	6.3x7.7	2.4	60
22	6.3x5.7 6.3x7.7	1.5 1.2	80 120	6.3x7.7 8x10.5	2.4 1.5	60 110	8x10.5	1.5	110
33	6.3x7.7 8x10.5	1.2 0.7	120 250	8x10.5	1.5	110	8x10.5 10x10.5	1.5 0.8	110 170
47	8x10.5	0.65	250	8x10.5	1.5	110	10x10.5	0.8	170
56	8x10.5	0.65	250	8x10.5	1.5	110	10x10.5	0.8	170
68	8x10.5	0.65	250	10x10.5	0.8	170	10x10.5	0.8	170
82	8x10.5 10x10.5	0.65 0.35	250 400	10x10.5	0.8	170			
100	10x10.5	0.35	400	10x10.5	0.8	170			
150	10x10.5	0.35	400						

Note1: Case size $\Phi D \times L$ (mm), ripple current (mA, rms) at 105°C, 100KHz.

Note2: Produce custom product too, which are not found in these tables.


■ Explanation of Part Numbers



(1-3)	(4-5)		(6-8)		(9)	(10-13)		
Series	Voltage (W.V)	Code	Capacitance (UF)	Code	Cap. Tolerance (%)	Code	Size ϕ DxL	Code
GVS	4	0G	0.1	0R1	+5	J	4x5(5.7)	0405
GVT	6.3	0J	0.22	0R22	-5		4x7	0407
GVE	10	1A	0.33	0R33	+10	K	5x5(5.7)	0505
GVZ	16	1C	0.47	0R47	-10		5x7	0507
GVM	25	1E	1	1R0	+15	L	5x11	0511
GVL	35	1V	2.2	2R2	-15		6.3x5(5.7)	0605
GVU	50	1H	3.3	3R3	+20	M	6.3x7(7.7)	0607
GVY	63	1J	4.7	4R7	-20		6.3x11	0611
GVF	80	1K	10	100	+30	N	8x5	0805
GVR	100	2A	22	220	-30		8x6.5	0806
GVG	125	2B	33	330	+20	V	8x9	0809
GVD	160	2C	47	470	-10		8x10(10.5)	0810
GVP	180	2Z	68	680	+30	Q	8x11(11.5)	0811
GVT	200	2D	100	101	-10		8x12	0812
GVC	220	2P	220	221	+50	T	10x10(10.5)	1010
GVN	250	2E	330	331	-10		10x12.5	1012
GVK	315	2F	470	471	+50	S	10x14	1014
GVA	330	2L	680	681	-20		12.5x13.5	1213
	350	2V	1000	102	+80	Z	12.5x16	1216
	400	2G	2200	222	-20		16x16.5	1616
	420	2Q	3300	332	+20	R	16x25	1625
	450	2W	4700	472	-0		20x25	2025
	500	2H	6800	682			35x42	3542


Taping Specifications

Carrier Tape



Case Size	W (mm)	W1 (mm)	F (mm)	P (mm)	P1 (mm)	P2 (mm)	A (mm)	B (mm)	t1 (mm)	t2 (mm)
$\phi 4 \times 5.7$	12	1.75	5.5	8	2	4	4.7	4.7	0.4	6.3
$\phi 5 \times 5.7$	12		5.5	12			6	6		6.3
$\phi 6.3 \times 5.7$	16		7.5	12			7	7		6.3
$\phi 6.3 \times 7.7$	16		7.5	12			7	7		8.3
$\phi 8 \times 6.5$	16		7.5	12			8.7	8.7		7
$\phi 8 \times 10.5$	24		11.5	16			8.7	8.7		11
$\phi 10 \times 10.5$	24		11.5	16			10.7	10.7	0.5	11
$\phi 10 \times 13.5$	24		11.5	16			10.7	10.7		14.1
$\phi 12.5 \times 13.5$	32		14.2	24			14	14		14.1
$\phi 12.5 \times 16$	32		14.2	24			14	14		16.4
$\phi 16 \times 16.5$	44		20.2	28			17.5	17.5		16.9
$\phi 16 \times 21.5$	44		20.2	28			17.5	17.5		21.9
$\phi 18 \times 16.5$	44		20.2	32			19.5	19.5		16.9
$\phi 18 \times 21.5$	44		20.2	32			19.5	19.5		21.9
Tolerance	± 0.3	± 0.15	± 0.1	± 0.1	± 0.1	± 0.1	± 0.2	± 0.2	± 0.1	± 0.2

Carrier Tape




Case Size	Reel	Carton	A ± 0.3	B ± 2	Case Size	Reel	Carton	A ± 0.3	B ± 2
$\phi 4 \times 5.7$	2000	20000	14	382	$\phi 10 \times 13.5$	300	3000	26	382
$\phi 5 \times 5.7$	1000	10000	14	382	$\phi 12.5 \times 13.5$	200	600	34	332
$\phi 6.3 \times 5.7$	1000	10000	18	382	$\phi 12.5 \times 16$	150	450	34	332
$\phi 6.3 \times 7.7$	1000	10000	18	382	$\phi 16 \times 16.5$	125	250	46	332
$\phi 8 \times 6.5$	1000	10000	18	382	$\phi 16 \times 21.5$	75	150	46	332
$\phi 8 \times 10.2$	500	5000	26	382	$\phi 18 \times 16.5$	125	250	46	332
$\phi 10 \times 10.2$	500	5000	26	382	$\phi 18 \times 21.5$	75	150	46	332

Reflow Soldering Conditions

Recommended soldering heat conditions

1. The following conditions are recommended for air convection and infrared reflow soldering on the SMD products onto a glass epoxy circuit boards by cream solder. The temperatures shown are the surface temperature values on the top of the can and on the capacitor terminals.
2. Reflow should be performed twice or less.
3. Please ensure that the capacitor became cold enough to the room temperature (5 to 35°C) before the second reflow.

Classification Reflow Profile




Notice:

1. Average ramp-up rate is 5°C/second max.
2. Ramp-down rate is 6°C/second max.
3. Time from 25°C to peak temperature is 6 minutes max.

	Preheat	Time maintained above 200°C	Time maintained above 220°C	Time maintained above 230°C	Peak temp.	Reflow number
Dia. 4~10mm general	120°C to 180°C 120 sec. Max.	60 sec.	50 sec.	30 sec.	250°C Max.	2 times or less
φ8x6.5		50 sec.	40 sec.	25 sec.	245°C Max.	2 times or less
WV 160v-450v		60 sec.	50 sec.	30 sec.	240°C Max.	2 times or less
Dia. 12.5~20mm Cap.		60 sec.	40 sec.	30 sec.	240°C Max.	2 times or less
125°C Category Temp.		60 sec.	40 sec.	30 sec.	250°C Max.	2 times or less

Recommended Solder Land Size on PC Board



Size	X	Y	a
φ4	1.6	2.6	1.0
φ5	1.6	3.0	1.4
φ6.3	1.6	3.5	2.1
φ8x6.5	1.6	4.5	2.1
φ8x10.5	2.5	3.5	3.0
φ10	2.5	4.0	4.0
φ12.5	3.0	5.7	4.0
φ16	3.5	6.5	6.0