




Technical Requirements:

1,100% continuity testing shall be performed on finished products: no short circuit, open circuit or misconnection is allowed.

2,Continuity resistance: 2Ω MAX

3,Insulation resistance: 10Ω MIN

4,Test voltage: 300VDC

5,Products comply with ROHS + REACH standards.

3.0 ± 0.3mm	Plating Sn	P1	Red
3.0 ± 0.3mm	Plating Sn	P2	White
3.0 ± 0.3mm	Plating Sn	P2	Yellow
3.0 ± 0.3mm	Plating Sn	P2	Black

Part		HY2.0-4Y/ plating Sn UL1007-26# L=100mm					
6							
5							
4							
3	Terminal	HY2.0 Plating Sn				4	pcs
2	Housing	HY2.0-4Y White				1	pcs
1	Wire	UL1007-26AWG R/B wire L=100mm,end plating Sn 3mm	103mm	1.0/3.0T		4	pcs
No.	Material	Description	Cut length of the wires	Set wire stripping length	wire length	QTY	Unit

贝迅泽 BEIXUNZE 贝迅泽技术（东莞）有限公司 BEIXUNZE TECHNOLOGY (DONGGUAN) CO., LTD				
www.hiemi.cn		PN:	HY2.0-4P-A-100-26A	
Drawn	CHC	Date	2024-11-19	A0
Check	LIKE	Date	2024-11-19	
Approved	WSR	Date	2024-11-19	