





技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):100V,AC.
- 3.额定电流(Rated current):1.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
- 6.耐压值(Withstanding voltage):500V AC/minute.



SECTION A-A





适用线路板(PCB LAYOUT)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Part No	CKT	A	B
AZH1.5-2A-22	2	1.5	4.5
AZH1.5-3A-22	3	3.0	6.0
AZH1.5-4A-22	4	4.5	7.5
AZH1.5-5A-22	5	6.0	9.0
AZH1.5-6A-22	6	7.5	10.5
AZH1.5-7A-22	7	9.0	12.0
AZH1.5-8A-22	8	10.5	13.5
AZH1.5-9A-22	9	12.0	15.0
AZH1.5-10A-22	10	13.5	16.5
AZH1.5-11A-22	11	15.0	18.0
AZH1.5-12A-22	12	16.5	19.5
AZH1.5-13A-22	13	18.0	21.0
AZH1.5-14A-22	14	19.5	22.5
AZH1.5-15A-22	15	21.0	24.0
AZH1.5-16A-22	16	22.5	25.5
AZH1.5-17A-22	17	24.0	27.0
AZH1.5-18A-22	18	25.5	28.5
AZH1.5-19A-22	19	27.0	30.0
AZH1.5-20A-22	20	28.5	31.5

序号	品名	材质			
①	ZH1.5弯针WTB胶芯	LCP UL94V-0 本色			
②	ZH1.5弯针WTB端子	铜合金/表面镀锡			
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.		TITLE:	
X.X±0.20		AZH1.5-NA-22		ZH1.5弯针WTB	
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olivia		MANUFACTURE DWG	
MATERILA	— — —	APPD: Ava		MANUFACTURE DWG	
FINISH	— — —			MANUFACTURE DWG	



NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弧形MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有的尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING.
(载带材料: 透明防静电 PS, 冷封.)
- 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.40 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 8.832 METERS. (每卷包装长度: 8.832米.)
- 7.COMPONENT LOAD PER REEL: 700 PCS. (每卷包装数量: 700只, 前后各空18只.)
- 8.纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充.
- 9.纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.



纸箱型号	小型	中型	标准型
Carton Type	Small Size	Medium	Standard
高度	7.5	15	32
Hight (CM)			

CKT	B0	W	F	S
(1.5mm pitch)				
2	4.80	16	7.50	
3	6.30			
4	7.80			
5	9.30			
6	10.80	24	11.50	
7	12.30			
8	13.80			
9	15.30			
10	16.80			
11	18.30	32	14.20±0.10	28.40
12	19.80			
13	21.30			
14	22.80			
15	24.30	44	20.20±0.10	40.40
16	25.80			
17	27.30			
18	28.80			
19	30.30			
20	31.80			

CKT	W	PCS/REEL	REEL/CARTON	SUM(PCS)
(1.5mm pitch)				
2	16	700	14	9800
3				
4				
5				
6	24	700	10	7000
7				
8				
9				
10				
11	32	700	8	5600
12				
13				
14				
15				
16	44	700	6	4200
17				
18				
19				
20				

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±2°	PART NO. AZH1.5-NA-22	TITLE: ZH1.5弯针WTB载带包装		
X.X±0.25					
X.XX±0.15					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERIAL	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 2/2