



技术指标(Technical Index):

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。

(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)

2. 工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.









3. 额定电压(Rated voltage): 250V, AC/DC.

4. 额定电流: 3.0A, AC/DC.

5. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.

6. 绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.

7. 耐电压(Withstanding Voltage): 800V AC/minute.



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B	C	D
APA2.0-2A-32	2	2.00	4.55	7.95	6.10
APA2.0-3A-32	3	4.00	6.55	9.95	8.10
APA2.0-4A-32	4	6.00	8.55	11.95	10.10
APA2.0-5A-32	5	8.00	10.55	13.95	12.10
APA2.0-6A-32	6	10.00	12.55	15.95	14.10
APA2.0-7A-32	7	12.00	14.55	17.95	16.10
APA2.0-8A-32	8	14.00	16.55	19.95	18.10
APA2.0-9A-32	9	16.00	18.55	21.95	20.10
APA2.0-10A-32	10	18.00	20.55	23.95	22.10
APA2.0-11A-32	11	20.00	22.55	25.95	24.10
APA2.0-12A-32	12	22.00	24.55	27.95	26.10
APA2.0-13A-32	13	24.00	26.55	29.95	28.10
APA2.0-14A-32	14	26.00	28.55	31.95	30.10
APA2.0-15A-32	15	28.00	30.55	33.95	32.10
APA2.0-16A-32	16	30.00	32.55	35.95	34.10

序号	品名	材质
①	2.0 R型卧式WTB胶芯 2.0 Pitch R/A Wire To Board Housing(H=5.7)	PA6T UL94V-0 米黄色 LCP UL94V-0 本色
②	2.0 R型立式WTB端子 2.0 Pitch S/T Wire To Board Terminal(H=8.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	2.0 R型卧式WTB焊片 2.0 Pitch R/A Wire To Board Fitting Nail(H=5.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
④	2.0 R型立式WTB吸盖 2.0 Pitch S/T Wire To Board Cover(H=8.7)	LCP UL94V-0 黑色/本色

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		APA2.0-NA-32	2.00 Pitch R型立式WTB		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				