





NOTES:

1.Specification:

- 1>.Operation force: 1000gf Max.
- 2>.Operation Temperature: -30° to $+85^{\circ}$.
- 3>.Storage Temperature: -40° to $+85^{\circ}$.
- 4>.Mechanical Life: 3000 cycles operations.
- 5>.Resistance to Soldering: $260\pm 5^{\circ}$ for 3-5 Seconds.

2.PLATING:

- 1>.GOLD flash 1u"(min) SOLDER TAIL,
3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>.Non-switch Rating: 100mA at 50V DC.
- 2>.Switching Rating: 25mA at 24V DC.
- 3>.Contact Resistance: Initial 50m Ω Max.
Contact Resistance: After life 100m Ω Max.
- 4>.Insulation Resistance: 100M Ω Min at 500VDC.
- 5>.Dielectric Strength: 500V AC for 60seconds.
- 6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DSIC XX L S G E R
↑ ↑ ↑ ↑ ↑
(包装方式: T=Tub R=Reel)
(电镀层: E=接触位 3u"/焊接位 1-2u")
(电镀层: G=端子内外电镀全金)
(端脚型: S=贴片 / D=插件 / J型)
(L=高柄 / S=低柄 / T=低柄贴胶)
(开关位数: 02位-----12位)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
>0±0.05	>0°±0.5°	PART NO. DSIC08LSGER	TITLE: PRODUCT Family DSIC Series Pitch 2.54mm		
>1±0.10	>5°±1.0°				
>10±0.30			MANUFACTURE DWG		
UNITS	mm	DESIGN:	Ethan		
MATERILA	---	CHED:	Olvia		
FINISH	---	APPD:	Ava		
				SCALE	SHEET
				N:A	1/1