





技术指标(Technical Index):

1. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2. 额定电压(Rated voltage):250V,AC.
3. 额定电流(Rated current):3.0A AC,DC.
4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值(Withstanding voltage):1000V AC/minute.
6. 绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B
AXH2.54-2A-12	2	2.5	7.5
AXH2.54-3A-12	3	5.0	10.0
AXH2.54-4A-12	4	7.5	12.5
AXH2.54-5A-12	5	10.0	15.0
AXH2.54-6A-12	6	12.5	17.5
AXH2.54-7A-12	7	15.0	20.0
AXH2.54-8A-12	8	17.5	22.5
AXH2.54-9A-12	9	20.0	25.0
AXH2.54-10A-12	10	22.5	27.5
AXH2.54-11A-12	11	25.0	30.0
AXH2.54-12A-12	12	27.5	32.5
AXH2.54-13A-12	13	30.0	35.0
AXH2.54-14A-12	14	32.5	37.5
AXH2.54-15A-12	15	35.0	40.0
AXH2.54-16A-12	16	37.5	42.5

序号	品名	材质
①	XH2.5直针WTB胶芯	LCP UL94V-0 米色 白色
②	XH2.5直针WTB端子	铜合金/表面镀锡
③	XH2.5立式吸盖	LCP UL94V-0 米色

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. AXH2.54-NA-12	TITLE: XH2.5直针WTB		
.X±0.20					
.XX±0.10			MANUFACTURE DWG		
UNITS	mm	DESIGN: Ethan			
MATERILA	— — —	CHED: Olivia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/2

