








技术指标:



1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC (=等效)。
4. 接触电阻: $50\text{m}\Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$ 。
6. 耐电压: 150V AC/Minute



序号	品名	材质
1	0.5掀盖立式胶芯(H=5.2)	LCP UL94V-0 本色
2	0.5掀盖立式后盖(H=5.2)	LCP UL94V-0 黑色
3	0.5掀盖立式端子(H=5.2)	铜合金/表面镀金
4	0.5掀盖立式焊片(H=5.2)	铜合金/表面镀锡

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM A	DIM B	DIM C	DIM D
JXT-FC05-LC5PH52	5	6.70	2.00	4.00	4.45
JXT-FC05-LC6PH52	6	7.20	2.50	4.50	4.95
JXT-FC05-LC7PH52	7	7.70	3.00	5.00	5.45
JXT-FC05-LC8PH52	8	8.20	3.50	5.50	5.95
JXT-FC05-LC9PH52	9	8.70	4.00	6.00	6.45
JXT-FC05-LC10PH52	10	9.20	4.50	6.50	6.95
JXT-FC05-LC11PH52	11	9.70	5.00	7.00	7.45
JXT-FC05-LC12PH52	12	10.20	5.50	7.50	7.95
JXT-FC05-LC13PH52	13	10.70	6.00	8.00	8.45
JXT-FC05-LC14PH52	14	11.20	6.50	8.50	8.95
JXT-FC05-LC15PH52	15	11.70	7.00	9.00	9.45
JXT-FC05-LC16PH52	16	12.20	7.50	9.50	9.95
.....					
JXT-FC05-LC66PH52	66	37.20	32.50	34.50	34.95
JXT-FC05-LC67PH52	67	37.70	33.00	35.00	35.45
JXT-FC05-LC68PH52	68	38.20	33.50	35.50	35.95
JXT-FC05-LC69PH52	69	38.70	34.00	36.00	36.45
JXT-FC05-LC70PH52	70	39.20	34.50	36.50	36.95



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		JXT-FC05-LCNPH52	0.5 Pitch掀盖立式带扣正脚(H=5.2)		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---				
			SCALE	SHEET	
			N:A	1/1	