



Dual N-Channel MOSFET RC6802

■ Features

- $V_{DS} (V) = 30V$
- $I_D = 3.5 A$ ($V_{GS} = 10V$)
- $R_{DS(ON)} < 50m\Omega$ ($V_{GS} = 10V$)
- $R_{DS(ON)} < 70m\Omega$ ($V_{GS} = 4.5V$)



■ Absolute Maximum Ratings $T_a = 25^\circ C$

Parameter		Symbol	Rating	Unit
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current	$T_A = 25^\circ C$	I_D	3.5	A
	$T_A = 70^\circ C$		3	
Pulsed Drain Current		I_{DM}	20	
Power Dissipation	$T_A = 25^\circ C$	P_D	1.15	W
	$T_A = 70^\circ C$		0.73	
Thermal Resistance.Junction- to-Ambient	$t \leq 10s$	R_{thJA}	110	$^\circ C/W$
	Steady-State		150	
Thermal Resistance.Junction- to-Lead		R_{thJL}	80	
Junction Temperature		T_J	150	$^\circ C$
Storage Temperature Range		T_{stg}	-55 to 150	

Dual N-Channel MOSFET

RC6802

■ Electrical Characteristics Ta = 25°C

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	V _{DSS}	I _D =250 μA, V _{GS} =0V	30			V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =30V, V _{GS} =0V			1	μA
		V _{DS} =30V, V _{GS} =0V, T _J =55°C			5	
Gate-Body Leakage Current	I _{GSS}	V _{DS} =0V, V _{GS} =±12V			±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250 μA	1.0		2.5	V
Static Drain-Source On-Resistance	R _{DS(on)}	V _{GS} =10V, I _D =3.5A			50	mΩ
		V _{GS} =10V, I _D =3.5A, T _J =125°C			77	
		V _{GS} =4.5V, I _D =2A			70	
On State Drain Current	I _{D(ON)}	V _{GS} =10V, V _{DS} =5V	20			A
Forward Transconductance	g _{FS}	V _{DS} =5V, I _D =3.5A		12		S
Input Capacitance	C _{iss}	V _{GS} =0V, V _{DS} =15V, f=1MHz		170	210	pF
Output Capacitance	C _{oss}			35		
Reverse Transfer Capacitance	C _{rss}			23		
Gate Resistance	R _g	V _{GS} =0V, V _{DS} =0V, f=1MHz	1.7		5.3	Ω
Total Gate Charge (10V)	Q _g	V _{GS} =10V, V _{DS} =15V, I _D =3.5A		4.05	5	nC
Total Gate Charge (4.5V)				2	3	
Gate Source Charge				0.55		
Gate Drain Charge				1		
Turn-On DelayTime	t _{d(on)}	V _{GS} =10V, V _{DS} =15V, R _L =4.2 Ω, R _G =3 Ω		4.5		ns
Turn-On Rise Time	t _r			1.5		
Turn-Off DelayTime	t _{d(off)}			18.5		
Turn-Off Fall Time	t _f			15.5		
Body Diode Reverse Recovery Time	t _{rr}	I _F = 3.5A, di/dt= 100A/us		7.5	10	nC
Body Diode Reverse Recovery Charge	Q _{rr}			2.5		
Maximum Body-Diode Continuous Current	I _S				1.5	A
Diode Forward Voltage	V _{SD}	I _S =1A, V _{GS} =0V			1	V

* The static characteristics in Figures 1 to 6 are obtained using <300us pulses, duty cycle 0.5% max.

Dual N-Channel MOSFET RC6802

■ Typical Characteristics




Fig 1: On-Region Characteristics (Note E)




Figure 2: Transfer Characteristics (Note E)




Figure 3: On-Resistance vs. Drain Current and Gate Voltage (Note E)




Figure 4: On-Resistance vs. Junction Temperature (Note E)




Figure 5: On-Resistance vs. Gate-Source Voltage (Note E)




Figure 6: Body-Diode Characteristics (Note E)

Dual N-Channel MOSFET

RC6802

■ Typical Characteristics




Figure 7: Gate-Charge Characteristics




Figure 8: Capacitance Characteristics




Figure 9: Maximum Forward Biased Safe Operating Area (Note F)




Figure 10: Single Pulse Power Rating Junction-to-Ambient (Note F)




Figure 11: Normalized Maximum Transient Thermal Impedance (Note F)