




技术指标(Technical Index):



1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
2. 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个。
(Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2)
3. 温度范围(Temperature range): -25°C~+85°C.
4. 额定电压(Rated voltage): 125V, AC/DC(=等效).
5. 接触电阻(Contact resistance): ≤0.02Ω.
6. 绝缘电阻(Insulation resistance): ≥100MΩ

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B	C
AMX1.25-2A-22	2	1.25	3.20	4.30
AMX1.25-3A-22	3	2.50	4.45	5.55
AMX1.25-4A-22	4	3.75	5.70	6.80
AMX1.25-5A-22	5	5.00	6.95	8.05
AMX1.25-6A-22	6	6.25	8.20	9.30
AMX1.25-7A-22	7	7.50	9.45	10.55
AMX1.25-8A-22	8	8.75	10.70	11.80
AMX1.25-9A-22	9	10.00	11.95	13.05
AMX1.25-10A-22	10	11.25	13.20	14.30
AMX1.25-11A-22	11	12.50	14.45	15.55
AMX1.25-12A-22	12	13.75	15.70	16.80
AMX1.25-13A-22	13	15.00	16.95	18.05
AMX1.25-14A-22	14	16.25	18.20	19.30
AMX1.25-15A-22	15	17.50	19.45	20.55
AMX1.25-16A-22	16	18.75	20.70	21.80
AMX1.25-17A-22	17	20.00	21.95	23.05
AMX1.25-18A-22	18	21.25	23.20	24.30
AMX1.25-19A-22	19	22.50	24.45	25.55
AMX1.25-20A-22	20	23.75	25.70	26.80




TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. AMX1.25-NA-22	TITLE: 1.25 Pitch A型弯针WTB		
X.X±0.20			MANUFACTURE DWG		
X.XX±0.10					
UNITS	mm	DESIGN: Ethan			
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/2



CKT (1.25mm pitch)	B0	W	F	S
2	4.60	16	7.50	
3	5.85			
4	7.10			
5	8.35			
6	9.60			
7	10.85	24	11.50	
8	12.10			
9	13.35			
10	14.60			
11	15.85			
12	17.10			
13	18.35	32	14.2±0.10	28.45
14	19.60			
15	20.85			
16	22.10			
17	23.35			
18	25.85	44	20.2±0.15	40.45
19	28.35			
20	30.85			

CKT (1.25mm pitch)	W	PCS/RELL	RELL/CARTON	SUM(PCS)
2	16	850	14	11900
3				
4				
5				
6				
7	24	850	10	8500
8				
9				
10				
11				
12				
13	32	850	8	6800
14				
15				
16				
17				
18	44	850	6	5100
19				
20				



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.50	±1°	PART NO.		TITLE:		
X.X±0.25		AMX1.25—NA—22		1.25—A型穿针WTB载带包装		
X.XX±0.15		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			SCALE	SHEET
MATERILA	— — —	APPD: Ava			N:A	2/2