

深圳市索瑞达电子有限公司

承 认 书 SPECIFICATION FOR APPROVAL

客户名称:

Customer Name : _____

客户料号:

Customer P/N: _____

产品名称: 功率电感

Product Name: _____

索瑞达料号:

Sorede P/N: SRTC.322510.YB系列

制造厂商 Manufacturer	
拟制 Draft	黄小香
审核 Check	深圳市索瑞达电子有限公司 符妃团 工程专用章
日期 Date	2025-06-25

客户承认印章 Approval Signet	
日期 Date	

地址:深圳市观澜镇福城街道新塘村8号源创园陆号A6栋3楼.

Address: 3Rd Floor, Building A6, Yuanchuangyuanlu, No. 8 Xintang Village, Fucheng Street, Guanlan Town, Shenzhen.

电话 Tel: 0755-29803356 传真 Fax: 0755-29803506

电子邮件 E-mail: sorde@vip.163.com


网址 http:// www.szsorede.com

修改履历表

Modify Resume

文件编号 File Number	SRD-WI-26113	版本号 Version Number	A	页码 page	1/6
---------------------	--------------	-----------------------	---	------------	-----

1、外形尺寸 Dimension :




单位Unit: mm

A	2.5±0.2
B	3.2±0.2
C	1.0Max
D	0.9Ref
E	1.0±0.2
F	3.25Ref
H	0.90Ref
G	2.55Ref


2、产品品名构成 Product Spec. Model

SRTC . 322510 . Y B 2R2 M T 00
 a b c d e f g h

- a: 系列名称 Series name
- b: 产品尺寸 Product dimensions (A x B x C)
- c: 密封方式 Sealing way (L: 冷封 Cold seal Y: 热封 Heat seal)
- d: 印字方向 Lettering direction ▶
- e: 电感值 Inductance Value
(1R0:1.0uH; 100: 10uH; 101:100uH)
- f: 电感公差 Inductance Tolerance (K:10% ; M:20% ; N:30%)
- g: 包装 Package (T:磁带/卷轴 Tape/Reel、 B: 散装 Bulk)
- h: 编号 Numbering (标准 standard)



3、结构 Structure



4、材料清单 MATERIAL LIST

NO.	PARTS	MATERIAL	UL FILE NO.	TEMP. CLASS
1	CORE	ALLOY POWDER OR EQUIVALENT/ (SH136)	NA	NA
2	WIRE	POLYESTER WIRE OR EQUIVALENT OR EQUIVALENT	NA	NA
3	Clip	100% PB FREE SOLDER OR EQUIVALENT	NA	NA
4	INK	HALOGEN-FREE KETONE OR EQUIVALENT	NA	NA

*NA:NOT APPLICABLE.

文件编号 File Number	SRD-WI-26113	版本号 Version Number	A	页码 page	2/6
---------------------	--------------	-----------------------	---	------------	-----

5、电性能参数表 Electrical Characteristics List

※公差Tolerance: N: $\pm 30\%$ 、M: $\pm 20\%$ 、K: $\pm 10\%$.


※工作温度 Operating temperature rang: -40 °C to +125°C (Including Self-heating)

※ 储存温度 Storage temperature rang: -40 °C to +125°C

额定电流：指使电感量比初始值下降30%TYP或电感器表面温度上升 40°C TYP 的电流值（参考周围环境温度 25°C）。 The rated DC current is that which cause at 30%TYP inductance reduction from the initial value or inductor surface temperature to rise by 40°C TYP, whichever is smaller (Reference ambient temperature 25°C)。


6. 产品包装 Packaging

1) 载带包装示意图 Tape packing diagram




ITEM	W	A0	B0	K0	P	E	F	D0	P1	P2	T
DIM	8.00	3.60	2.80	1.20	4.00	3.50	1.75	1.50	4.00	2.00	0.35
TOLE	± 0.3	± 0.1	$+0.1$	± 0.1	± 0.1	± 0.05					

2) 卷盘包装示意图 Tape packing diagram



A	180 ± 0.5
B	100 ± 0.5
C	13.5 ± 0.5
W	8.5 ± 0.5

3) 卷盘包装示意图 Tape packing diagram




文件编号 File Number	SRD-WI-26113	版本号 Version Number	A	页码 page	4/6
---------------------	--------------	-----------------------	---	------------	-----


4) 剥离强度要求Peeling required

①F 力大小: 20~100g;

②面带剥离角度: 165°~180°。



5) 包装数量 Packing quantity



项目 (Project)	数量 (PCS)	尺寸规格 (Size:mm)
盘(Reel)	3000	7"
内盒 (Inner box)	30K	185mm*185mm*120mm
外箱 (Out box)	180K	395mm*385mm*205mm

文件编号 File Number	SRD-WI-26113	版本号 Version Number	A	页码 page	5/6
Mechanical Reliability					
TEST ITEM	SPECIFICATION	TEST DETAILS			
Mechanical shock	1. No case deformation or change in appearance 2. $\Delta L/L_0 \leq \pm 10\%$	1. Acceleration: 100G 2. Pulse time: 6ms 3. Direction: $\pm X \pm Y \pm Z$ 4. 3 times in each positive and negative direction of 3 mutual perpendicular directions			
Mechanical vibration	1. No case deformation or change in appearance 2. $\Delta L/L_0 \leq \pm 10\%$	1. Reflow: 2 times 2. Frequency: 10HZ~55HZ~10HZ, 20 Min/Cycles 3. Amplitude: 1.52 mm 4. Directions: X, Y, Z 5. Time: 12 cycle / direction			
Solderability	1. No case deformation or change in appearance 2. New solder coverage More than 95%	1. Preheat: $155^{\circ}\text{C} \pm 5^{\circ}\text{C}$, 60S $\pm 2\text{S}$ 2. Tin: lead-free. 3. Temperature: $240^{\circ}\text{C} \pm 5^{\circ}\text{C}$, flux $3.0\text{S} \pm 0.5\text{S}$.			
Endurance Reliability					
Thermal Shock	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	1. First -55°C for 30 minutes, last 125°C for 30 minutes as 1 cycle. Go through 1000 cycles. 2. Max transfer time is 3 minutes. 3. Measured at room temperature after placing for 24 ± 2 hours			
		1		Temperature	Duration
		2		$-55 \pm 2^{\circ}\text{C}$ (Thermostat No.1)	30 min.
		3		Standard atmospheric No.1 \rightarrow No.2	Within 3 minutes
		4		$125 \pm 2^{\circ}\text{C}$ (Thermostat No.2)	30 min.
Humidity Resistance	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	1. Reflow 2 times, $2.85^{\circ}\text{C}, 85\%RH, 1000$ hours 3. Measured at room temperature after placing for 24 ± 2 hours			
Low temperature storage	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	1. Temperature: $-55 \pm 2^{\circ}\text{C}$ 2. Time: 1000 hours 3. Measured at room temperature after placing for 24 ± 2 hours			
High temperature storage	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	1. Temperature: $+125 \pm 2^{\circ}\text{C}$ 2. Time: 1000 hours 3. Measured at room temperature after placing for 24 ± 2 hours			

文件编号 File Number	SRD-WI-26113	版本号 Version Number	A	页码 page	6/6
---------------------	--------------	-----------------------	---	------------	-----

8、注意事项 Note

①本承认书保证我司产品作为一个单体时的质量情况。当我司产品被安装到贵司产品上时，请保证贵司的产品已根据贵司的规范进行了有效评估和确认。

This product specification guarantees the quality of our product as a single unit. Please make sure that your product is evaluated and confirmed against your specifications when our product is mounted to your product.

②如果贵司对我司产品的使用已超过了本承认书所界定的产品功能，那么对于由此引发的失效，我司将不予保证。

We cannot warrant against failure caused by any use of our product that deviates from the intended use as described in this product specification.

③为了保持终端电极的焊接性，并使包装材料保持良好状态，必须控制储存区的温度和湿度。

To maintain the solderability of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled.

※建议的条件: -10 ~ +40°C, 30~70%RH。

Recommended conditions: -10 ~ +40°C, 30~70%RH.

※储存超过六个月的，应在实际使用前进行焊接检验。

In case of storage over 6 months, solderability shall be checked before actual usage.

※即使在理想的储存条件下，产品的可焊性也随着时间的推移而降低。因此，产品应从交货时算起，建议8个月之内使用完。

Even under ideal storage conditions, the weldability of the product decreases over time. therefore, the product should be from the time of delivery, it is recommended that it be used within 8 months.

④本承认书在客户收到30天之内，必须签章返回，逾期视为默认。

The Specification Approval should be sent back to the supplier with customer's shop on it within 30 days after receiving it, or we will take it as approved by customer's automatically.

⑤如有特殊规格要求，请事前联络我司技术部人员。

In case of special specifications please contact our technical department prior staff.