

20A SCHOTTKY BARRIER RECTIFIER

General Description

MBRD2060CT Device optimized for ultra-low forward voltage drop to maximize efficiency in Power Supply applications

Features

- Low Leakage Current
- High Current Capability, High Efficiency
- High Junction Temperature Capability
- RoHS Compliant


Product Summary

V _{RRM}	V _F	I _{F(AV)}
60V	0.79V	20A

Applications

- Low Voltage High Frequency Switching Power Supply
- Low Voltage High Frequency Invers Circuit
- Low Voltage Continued Circuit and Protection Circuit

TO-252 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{RRM}	Peak Repetitive Reverse Voltage	60	V
I _{F(AV)}	Average Rectified Forward Current (Rated VR-20Khz Square Wave) - 50% duty cycle	10 (Per Leg) 20 (Total)	A
dv/dt	Voltage rate of change (Rated VR)	10000	V/uS
I _{RRM}	Peak Repetitive Reverse Surge Current (2uS,1Khz)	0.5	A
I _{FSM}	Forward Peak Surge Current(Rated Load 8.3ms Half Mssine Wave-According to JEDEC Method)	360	A
T _J	Operating Junction Temperature	150	°C
T _{STG}	Storage Temperature	-40 to 150	°C


Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJC}	Thermal Resistance, Junction to Case(Per Leg)	3	---	°C/W


Electrical Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
V_F	Forward Voltage Drop per diode	$I_F=10A, T_c=25^{\circ}C \ I_F(AV)=10A*2$	---	0.71	0.79	V
		$I_F=10A, T_c=125^{\circ}C \ I_F(AV)=10A*2$	---	---	0.72	
I_R	Reverse Leakage Current per diode	$V_R=60V, T_c=25^{\circ}C$	---	---	0.03	mA
		$V_R=60V, T_c=125^{\circ}C$	---	---	8.00	mA


Typical Performance Characteristics



Current derating curve, per element



The forward voltage and forward current curve



The reverse leak current and the reverse voltage (single-device) curve

This product has been designed and qualified for the consumer market.
 Cmos assumes no liability for customers' product design or applications.
 Cmos reserves the right to improve product design, functions and reliability without notice. Please refer to the latest version of specification.