


1.Features

- Plastic Package has Underwriters Laboratory
- Flammability Classification 94V-0
- Metal silicon junction, majority carrier conduction
- For surface mount applications
- Guard ring for overvoltage protection
- Low power loss, high efficiency
- High current capability, Low forward voltage drop
- High surge capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- High temperature soldering guaranteed : 250°C/10 seconds at terminals

2.Mechanical Data

- Case : JEDEC SMA(DO-214AC) molded plastic body
- Terminals : Solder Plate, solderable per
- MIL-STD-750, Method 2026
- Polarity : Color band denotes cathode end
- Weight : 0.003 ounce, 0.093 gram

3.Pinning information





4. Maximum Ratings And Electrical Characteristics

Parameter		Symbols	SS 32A	SS 33A	SS 34A	SS 35A	SS 36A	SS 38A	SS 310A	SS 315A	SS 320A	Units
Maximum repetitive peak reverse voltage		V _{RRM}	20	30	40	50	60	80	100	150	200	V
Maximum RMS voltage		V _{RMS}	14	21	28	35	42	56	71	105	140	V
Maximum DC blocking voltage		V _{DC}	20	30	40	50	60	80	100	150	200	V
Maximum Average Forward Rectified Current		I _{F(AV)}	3									A
Peak Forward Surge Current, 8.3 ms Single Half Sinewave Superimposed on Rated Load (JEDEC method)		I _{FSM}	100			70						A
Maximum instantaneous forward voltage at 3.0 A(Note 1)	T _A =25°C	V _F	0.5			0.75		0.85		0.95		V
	T _A =100°C		0.4			0.65		0.70		0.80		V
Maximum Reverse Current @ Rated V _R	T _A =25°C	I _R	0.5				0.1				mA	
	T _A =100°C		10		5		2				mA	
	T _A =125°C						0.5				mA	
Typical thermal resistance		R _{θJL}	17									°C/W
		R _{θJA}	55									°C/W
Junction Temperature Range		T _J	-55 to 125			-55 to 150						°C
Storage Temperature Range		T _{STG}	-55 to 150									°C

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Notes:

1: Pluse Test with PW=300 usec, 1% Duty Cycle.



5. Typical characteristic




Figure 1: Forward Current Derating Curve




Figure 2: Maximum Non-repetitive Peak Forward Surge Current




Figure 3: Typical Forward Characteristics




Figure 4: Typical Reverse Characteristics




Figure 5: Typical Junction Capacitance





Figure 6: Typical Transient Thermal Impedance



6.SMA Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	B	b	c	D	E	e1	L	K	θ
Min	1.95	0.77	0.97	1.10	4.95	2.00	2.09	1.38	1.95	4.25	2.60	0°
Max	2.05	0.83	1.03	1.30	5.15	2.20	2.19	1.42	2.05	4.35	2.65	5°

Notes: e-H<0.15mm



7 .Ordering information



Order Code	Marking	Package	Base QTY	Delivery Mode
UMW SS32A	SS32	SMA	2000	Tape and reel
UMW SS33A	SS33	SMA	2000	Tape and reel
UMW SS34A	SS34	SMA	2000	Tape and reel
UMW SS35A	SS35	SMA	2000	Tape and reel
UMW SS36A	SS36	SMA	2000	Tape and reel
UMW SS38A	SS38	SMA	2000	Tape and reel
UMW SS310A	SS310	SMA	2000	Tape and reel
UMW SS315A	SS315	SMA	2000	Tape and reel
UMW SS320A	SS320	SMA	2000	Tape and reel



8.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.