


图面产品均符合ROHS标准

Technical drawing of a bolt head and nut assembly. The bolt head is at the top with a width of SQ6.50 and a height of 8.50. The nut is below it with a height of 16.60 ± 0.030. The nut has a width of Ø7.70. A surface finish symbol H8.00 is indicated on the nut's side.



- 1) 标准阻抗: 50 OHM;
- 2) 频率范围: 0-6 GHz;
- 3) 电压驻波比: 2.0 MAX;
- 4) 工作电压: 335-500 VOLTS;
- 5) 电介质耐电压: 500-1500 VRMS;
- 6) 螺牙与本体的装配后要能轻松转动;
- 7) 六角旋转体表面不能有压碰伤和变形;
- 8) 中心针剖口对准横孔方向;
- 9) 其它外观要求依我司品管标准管控;

D	7	压 盖	C1303172 / QT001-AU	黄铜3604	1	镀金 1u"	φ5.00 X 0.80
	6	本 体	C501173 / BT010-AU	黄铜3604	1	镀金 1u"	13.50 X 13.95
	5	PIN 针	C1303173 / PIN007-AU	黄铜3604	1	镀金 1u"	φ1.80 X 13.30
	4	绝缘体	C107184 / JYT004-00	铁氟龙	1	素 材	φ4.09 X 7.50
	3	C 形环	C1303715 / WH334-00	磷 铜	1	素 材	φ7.40 X 0.90
	2	胶 圈	C107171 / JQ002-00	硅 胶	1	暗红色	φ6.00 X 0.70
E	1	旋转体	C1303060 / XZT006-AU	黄铜3604	1	镀金 1u"	H8.00 X 8.50
	序号	名 称	零件料号	材 质	数量	表面处理	产品规格

B O M 表

ZKT® 深圳市中科无线技术有限公司

公 差	x.±0.30 x.x±0.20 x.xx±0.10 ANGULAR 5°				代 码		料 号		
					品 名	YG025-A7M1-000 SMA六角弯公头公针			
		变 更 记 录		日 期	变更者	型 号	ZKC502036		
		比 例	1： 3	纸 张	A4	绘 图	ZHANG	日 期	2026. 01. 03
图 法		单 位	mm	版 本	A	审 核		确 认	