






技术指标 (Technical Index):

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
- 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个。
(Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2)
- 温度范围 (Temperature range): -25°C ~ +85°C.
- 额定电流 (Rated Current): 1A AC/DC
- 额定电压 (Rated voltage): 125V, AC/DC (=等效).
- 接触电阻 (Contact resistance): ≤0.02Ω.
- 绝缘电阻 (Insulation resistance): ≥100MΩ





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B	C
AMX1.25-2A-12	2	1.25	3.20	4.30
AMX1.25-3A-12	3	2.50	4.45	5.55
AMX1.25-4A-12	4	3.75	5.70	6.80
AMX1.25-5A-12	5	5.00	6.95	8.05
AMX1.25-6A-12	6	6.25	8.20	9.30
AMX1.25-7A-12	7	7.50	9.45	10.55
AMX1.25-8A-12	8	8.75	10.70	11.80
AMX1.25-9A-12	9	10.00	11.95	13.05
AMX1.25-10A-12	10	11.25	13.20	14.30
AMX1.25-11A-12	11	12.50	14.45	15.55
AMX1.25-12A-12	12	13.75	15.70	16.80
AMX1.25-13A-12	13	15.00	16.95	18.05
AMX1.25-14A-12	14	16.25	18.20	19.30
AMX1.25-15A-12	15	17.50	19.45	20.55
AMX1.25-16A-12	16	18.75	20.70	21.80
AMX1.25-17A-12	17	20.00	21.95	23.05
AMX1.25-18A-12	18	21.25	23.20	24.30
AMX1.25-19A-12	19	22.50	24.45	25.55
AMX1.25-20A-12	20	23.75	25.70	26.80

序号	品名	材质
①	A型立式DIP型WTB胶芯 1.25 Pitch S/T Wire To Board Housing DIP(H=4.7)	LCP UL94V-0 本色 Natural
②	A型立式DIP型WTB端子 1.25 Pitch S/T Wire To Board Terminal DIP(H=4.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	A型立式DIP型WTB吸盖 1.25 Pitch S/T Wire To Board Cap	LCP UL94V-0 本色

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		AMX1.25-NA-12	1.25 Pitch A型直针WTB		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —				
			SCALE	SHEET	
			N:A	1/2	



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.50	±1°	PART NO.		TITLE:		
X.X±0.25		AMX1.25—NA—12		1.25—A型直针WTB载带包装		
X.XX±0.15		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olvia				
MATERILA	— — —	APPD: Ava			SCALE	SHEET
FINISH	— — —				N:A	2/2