






技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):200V,AC.
- 3.额定电流(Rated current):2.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 25\text{m}\Omega$.
- 5.耐压值(Withstanding voltage):500V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B
AHY2.0-2A-12	2	2.0	6.0
AHY2.0-3A-12	3	4.0	8.0
AHY2.0-4A-12	4	6.0	10.0
AHY2.0-5A-12	5	8.0	12.0
AHY2.0-6A-12	6	10.0	14.0
AHY2.0-7A-12	7	12.0	16.0
AHY2.0-8A-12	8	14.0	18.0
AHY2.0-9A-12	9	16.0	20.0
AHY2.0-10A-12	10	18.0	22.0
AHY2.0-11A-12	11	20.0	24.0
AHY2.0-12A-12	12	22.0	26.0
AHY2.0-13A-12	13	24.0	28.0
AHY2.0-14A-12	14	26.0	30.0
AHY2.0-15A-12	15	28.0	32.0
AHY2.0-16A-12	16	30.0	34.0
AHY2.0-17A-12	17	32.0	36.0
AHY2.0-18A-12	18	34.0	38.0
AHY2.0-19A-12	19	36.0	40.0
AHY2.0-20A-12	20	38.0	42.0



序号	品名	材质	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
①	HY2.0直针WTB胶芯	LCP UL94V-0 本色	X.±0.50	±1°	PART NO. AHY2.0-NA-12	TITLE: HY2.0直针WTB			
			X.X±0.20						
			X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG			
②	HY2.0直针WTB端子	铜合金/表面镀锡	UNITS	mm					
③	2.00 F型立式2代WTB吸盖	LCP UL94V-0 本色	MATERILA	— — —	CHED: Olvia		SCALE N:A	SHEET 1/2	
			FINISH	— — —	APPD: Ava				

