





技术指标(Technical Index):



- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):200V,AC.
- 3.额定电流(Rated current):2.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 25\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.耐压值(Withstanding voltage):1000V AC/minute.



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B	C	D
AHY2.0-2A-22	2	2.0	6.0	4.84	2.4
AHY2.0-3A-22	3	4.0	8.0	6.84	2.4
AHY2.0-4A-22	4	6.0	10.0	8.84	4.4
AHY2.0-5A-22	5	8.0	12.0	10.84	6.4
AHY2.0-6A-22	6	10.0	14.0	12.84	8.4
AHY2.0-7A-22	7	12.0	16.0	14.84	10.4
AHY2.0-8A-22	8	14.0	18.0	16.84	12.4
AHY2.0-9A-22	9	16.0	20.0	18.84	14.4
AHY2.0-10A-22	10	18.0	22.0	20.84	16.4
AHY2.0-11A-22	11	20.0	24.0	22.84	18.4
AHY2.0-12A-22	12	22.0	26.0	24.84	20.4
AHY2.0-13A-22	13	24.0	28.0	26.84	22.4
AHY2.0-14A-22	14	26.0	30.0	28.84	24.4
AHY2.0-15A-22	15	28.0	32.0	30.84	26.4
AHY2.0-16A-22	16	30.0	34.0	32.84	28.4
AHY2.0-17A-22	17	32.0	36.0	34.84	30.4
AHY2.0-18A-22	18	34.0	38.0	36.84	32.4
AHY2.0-19A-22	19	36.0	40.0	38.84	34.4
AHY2.0-20A-22	20	38.0	42.0	40.84	36.4

序号	品名	材质							
①	HY2.0弯针WTB胶芯	LCP UL94V-0 本色							
②	HY2.0弯针WTB端子	铜合金／表面镀锡							
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd							
X.±0.50	±1°	PART NO.		TITLE:					
X.X±0.20		AHY2.0-NA-22		HY2.0弯针WTB					
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG					
UNITS	mm	CHED: Olvia							
MATERILA	— — —	APPD: Ava							
FINISH	— — —				<table><tr><td>SCALE</td><td>SHEET</td></tr><tr><td>N:A</td><td>1/2</td></tr></table>	SCALE	SHEET	N:A	1/2
SCALE	SHEET								
N:A	1/2								



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd.	
X.±0.50	±1°	PART NO. AHY2.0-NA-22	TITLE: HY2.0弯针WTB载带包装
X.X±0.25			
X.XX±0.15			
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG  SCALE N:A SHEET 2/2
MATERILA	— — —	CHED: Olvia	
FINISH	— — —	APPD: Ava	