






SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
FH2.54-02-01PWS	1	0.00	2.54
FH2.54-02-02PWS	2	2.54	5.08
FH2.54-02-03PWS	3	5.08	7.62
FH2.54-02-04PWS	4	7.62	10.16
FH2.54-02-05PWS	5	10.16	12.70
FH2.54-02-06PWS	6	12.70	15.24
FH2.54-02-07PWS	7	15.24	17.78
FH2.54-02-08PWS	8	17.78	20.32
FH2.54-02-09PWS	9	20.32	22.86
.....			
FH2.54-02-40PWS	40	(PIN-1)X2.54	(PIN)X2.54



PART NUMBER DESCRIPTION:


FH2.54-02-NPWS

(D=单排;S=双排)

(Z=直脚;W=弯脚)

(PIN数量;01.....40PIN)

(排针开关)



PCB TOLERANCE:±0.05 (TOP VIEW)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.54FH H8.5 2xnPin SMT U型 PC7.2 PB8.8 6T
			PAR FH2.54-02-NPWS
DECIMALS:	ANGLES:		DWN
X.±0.30	X°±5'		CHKD
X.X±0.20	X.X°±1'	CUSTOMER COPY	APVD
X.XX±0.10	X.XX°±0.5'		SCALE N:A UNIT:MM
		SIZE:A4	SHEET:1F1 REV:A