


SOT-323 Bipolar Transistor 双极型三极管

■Features 特点

NPN Switching 开关

■Absolute Maximum Ratings 最大额定值

HF RoHS Pb



Characteristic 特性参数	Symbol 符号	Rat 额定值	Unit 单位
Collector-Base Voltage 集电极基极电压	V_{CBO}	60	V
Collector-Emitter Voltage 集电极发射极电压	V_{CEO}	40	V
Emitter-Base Voltage 发射极基极电压	V_{EBO}	6	V
Collector Current 集电极电流	I_C	200	mA
Power dissipation 耗散功率	$P_C(T_a=25^{\circ}C)$	200	mW
Thermal Resistance Junction-Ambient 热阻	$R_{\theta JA}$	625	$^{\circ}C/W$
Junction and Storage Temperature 结温和储藏温度	T_J, T_{stg}	-55to+150 $^{\circ}C$	

■Device Marking 产品打标






MMBT3904W-6AF=K2N

■Electrical Characteristics 电特性


(TA=25°C unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	Min 最小值	Type 典型值	Max 最大值	Unit 单位
Collector-Base Breakdown Voltage 集电极基极击穿电压(IC=10uA, IE=0)	BV _{CBO}	60	—	—	V
Collector-Emitter Breakdown Voltage 集电极发射极击穿电压(IC=1mA, IB=0)	BV _{CEO}	40	—	—	V
Emitter-Base Breakdown Voltage 发射极基极击穿电压(IE=10uA, IC=0)	BV _{EBO}	6	—	—	V
Collector-Base Leakage Current 集电极基极漏电流(V _{CB} =60V, IE=0)	I _{CBO}	—	—	60	nA
Collector-Emitter Leakage Current 集电极发射极漏电流(V _{CE} =30V, V _{BE} =-3V)	I _{CEX}	—	—	50	nA
Emitter-Base Leakage Current 发射极基极漏电流(V _{EB} =5V, IC=0)	I _{EBO}	—	—	60	nA
DC Current Gain(V _{CE} =1V, IC=1mA) 直流电流增益(V _{CE} =1V, IC=10mA) (V _{CE} =1V, IC=50mA)	H _{FE}	70 100 60	—	300	
Collector-Emitter Saturation Voltage 集电极发射极饱和压降(IC=50mA, IB=5mA)	V _{CE(sat)}	—	—	0.3	V
Base-Emitter Saturation Voltage 基极发射极饱和压降(IC=50mA, IB=5mA)	V _{BE(sat)}	—	—	0.95	V
Transition Frequency 特征频率(V _{CE} =20V, IC=10mA)	f _T	300	—	—	MHz
Delay Time 延迟时间 (V _{CC} =3V, V _{BE} =-0.5V, IC=10mA, IB1=1mA)	t _d	—	—	35	ns
Rise Time 上升时间 (V _{CC} =3V, V _{BE} =-0.5V, IC=10mA, IB1=1mA)	t _r	—	—	35	ns
Storage Time 贮存时间 (V _{CC} =3V, IC=10mA, IB1=IB2=1mA)	t _s	—	—	200	ns
Fall Time 下降时间 (V _{CC} =3V, IC=10mA, IB1=IB2=1mA)	t _f	—	—	50	ns

■ Typical Characteristic Curve 典型特性曲线



■Dimension 外形封装尺寸



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.200	0.400	0.008	0.016
c	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
e	0.650 TYP		0.026 TYP	
e1	1.200	1.400	0.047	0.055
L	0.525 REF		0.021 REF	
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°