






The bottom of the page features the 'JXT COIN' logo in a large, stylized, orange font. To the right of the logo is a detailed line drawing of a coin slot machine's internal mechanism, showing a coin being inserted into a slot and the associated mechanical parts.

NO.	PART NAME	Q'TY	MATERIAL	FINISH	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
							PART NO.	TITLE:			
1	Shell	1	SUS304-1/2H,T=0.30mm	50u"Ni Min.	X.±0.50	X.*±5°	TYPE-C-FGB389	TYPE-C Vertical Type Double Row SMT REC	MANUFACTURE DWG		
2	TERMINAL	2	C7025 TM04,T=0.12mm	1u"Au/50u"Ni Min.	X.X±0.35	X.X*±3°					
3	MID PLATE	1	SUS301-H,T=0.15mm	wash	X.XX±0.25	X.XX*±2.5°					
4	GROUND PLATE	2	SUS301-H,T=0.10mm	wash	UNITS	mm	DESIGN:	Ethan	SCALE		
5	Housing	1	LCP	UL 94 V-0	MATERILA	— — —	CHED:	Olvia			
					FINISH	— — —	APPD:	Ava	N:A		
								1/3			

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$
 RECOMMENDED PCB THICKNESS: $0.8\pm 0.10\text{mm}$

USB TYPE-C 16PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

SPECIFICATION:

- MATERIAL:
 - HOUSING&MOLDING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0 COLOR:BLACK
 - CONTACTS:COPPER ALLOY T=0.12mm
 - SHELL:STAINLESS STEEL SUS304-1/2H,T=0.30
 - MID PLATE: STAINLESS STEEL(SUS301)T=0.15mm
 - EMI PLATE: STAINLESS STEEL(SUS301)T=0.10mm
- PLATING SPECIFICATION:
 - CONTACTS:
 - Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE MATING AREA OF CONTACT.
MATTE SN PLATED ON THE SOLDER AREA.
 - SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.
 - MID PLATE:CLEAR ONLY
 - EMI PLATE:CLEAR ONLY
- MECHANICAL:
 - MATING FORCE:0.5~2.0kgf;
 - UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY TEST;
 - DURABILITY:10000 CYCLES;
- ELECTRICAL:
 - CURRENT RATING:5A Max;
 - VOLTAGE RATING:20V Max;
 - DIELECTRIC WITHSTANDING VOLTAGE:100VAc;
 - CONTACT RESISTANCE:40m Ohms Max.;
 - INSULATION RESISTANCE:100M Ohms Min.;
- ENVIRONMENTAL:
 - OPERATING TEMPERATURE:-40°C~+85°C;
 - WETTING TEMPERATURE:265±5°C,5±0.5s

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	X.*±5°	PART NO. TYPE-C-FGB389	TITLE: TYPE-C Vertical Type Double Row SMT REC		
X.X±0.35	X.X*±3°				
X.XX±0.25	X.XX*±2.5°		MANUFACTURE DWG		
UNITS	mm	DESIGN: Ethan			
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	2/3

