


FEATURES

- ◆ Adoption of MBIT processes.
- ◆ Low collector-to-emitter saturation voltage.
- ◆ Fast switching speed.
- ◆ Large current capacity and wide ASO.
- ◆ Complementary to PBSS5350X,115-JSM



SOT-89

MAXIMUM RATING (Ta=25℃)


CHARACTERISTIC	SYMBOL	RATING	UNIT
Collector-Base Voltage	V _{CB0}	60	V
Collector-Emitter Voltage	V _{CE0}	50	V
Emitter-Base Voltage	V _{EB0}	6	V
Collector Current	I _c	3	A
Collector Current(Pulse)	I _{CP}	6	A
Collector Power Dissipation	P _c	500	mW
	P _c *	1	W
Junction Temperature	T _j	150	℃
Storage Temperature Range	T _{stg}	-55~150	℃

* : Package mounted on ceramic substrate(250mm²0.8t)×


Electrical characteristics(Ta=25℃)

Symbol	Test condition		Rating			Unit
			Min	Typ	Max	
V _{CB0}	I _c =10μA	I _E =0	60			V
V _{CE0}	I _c =1.0mA	I _B =0	50			V
V _{EB0}	I _E =10μA	I _c =0	6.0			V
I _{CB0}	V _{CB} =40V	I _E =0			1.0	μA
I _{EB0}	V _{EB} =4.0V	I _c =0			1.0	μA
h _{FE} (1)	V _{CE} =2.0V	I _c =100mA	100		400	
h _{FE} (2)	V _{CE} =2.0V	I _c =3.0A	35			
V _{CE(sat)}	I _c =2.0A	I _B =100mA		0.19	0.5	V
V _{BE(sat)}	I _c =2.0A	I _B =100mA		0.94	1.2	V
f _r	V _{CE} =10V	I _c =50mA		150		MHz
C _{cb}	V _{CB} =10V	I _E =0		25		pF
t _{on}	101B~101B-I _c =1.0A			70		nS
t _{stg}				650		nS
t _f				35		nS

Electrical characteristic curves



SOT-89



DIM	MILLIMETERS
A	4.70 MAX
B	2.50±0.20
C	1.70 MAX
D	0.45+0.15/-0.10
E	4.25 MAX
F	1.50±0.10
G	0.40 TYP
H	1.7 MAX
J	0.7 MIN
K	0.5+0.15/-0.10

Revision History

Rev.	Change	Date
V1.0	Initial version	2/23/2024

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com