







3D View



METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)

NOTES:

1:MATERIAL

1-1: SUS-301 THICKNE=0.15MM

2:SPECIFICATIONS

2-1: CONTACT RESISTANCE: 80mΩ/MAX

2-2: RATED CURRENT: 1.0A

2-3: VOLTAGE RATING: 1.5V

2-4: WELDING THRUST: ≥3KG

2-5: CLAMPING FORCE:60-120g

2-6: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 200 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE6-2:ROHS、REACH、HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS

深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: H1. 2mm 线夹	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW09-12F-120B	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2601191640	
			SHEET NO. 1 OF 1	