


SOT-23-3L -20V P Channel Enhancement 沟道增强型
MOS Field Effect Transistor 场效应管



■ **Absolute Maximum Ratings 最大额定值**

Characteristic 特性参数	Symbol 符号	Rat 额定值	Unit 单位
Drain-Source Voltage 漏极-源极电压	BV_{DSS}	-20	V
Gate- Source Voltage 栅极-源极电压	V_{GS}	± 10	V
Drain Current (continuous)漏极电流-连续	I_D (at $T_A = 25^\circ\text{C}$)	-5.5	A
Drain Current (pulsed)漏极电流-脉冲	I_{DM}	-23	A
Total Device Dissipation 总耗散功率	P_D (at $T_A = 25^\circ\text{C}$)	1200	mW
Thermal Resistance Junction-Ambient 热阻	$R_{\theta JA}$	105	$^\circ\text{C}/\text{W}$
Junction/Storage Temperature 结温/储存温度	T_J, T_{stg}	-55~150	$^\circ\text{C}$

■ **Device Marking 产品字标**

SI2305L3-6AF=A5

■ Electrical Characteristics 电特性

 (T_A=25℃ unless otherwise noted 如无特殊说明, 温度为 25℃)

Characteristic 特性参数	Symbol 符号	Min 最小值	Typ 典型值	Max 最大值	Unit 单位
Drain-Source Breakdown Voltage 漏极-源极击穿电压(I _D = -250uA, V _{GS} =0V)	BV _{DSS}	-20	—	—	V
Gate Threshold Voltage 栅极开启电压(I _D = -250uA, V _{GS} = V _{DS})	V _{GS(th)}	-0.4	-0.62	-1	V
Zero Gate Voltage Drain Current 零栅压漏极电流(V _{GS} =0V, V _{DS} = -20V)	I _{DSS}	—	—	1	uA
Gate Body Leakage 栅极漏电流(V _{GS} =±10V, V _{DS} =0V)	I _{GSS}	—	—	±100	nA
Static Drain-Source On-State Resistance 静态漏源导通电阻(I _D = -5A, V _{GS} = -4.5V) (I _D = -4A, V _{GS} = -2.5V) (I _D = -3A, V _{GS} = -1.8V)	R _{DS(ON)}	—	29 35 45	42 55 75	mΩ
Diode Forward Voltage Drop 内附二极管正向压降(I _{SD} = -5A, V _{GS} =0V)	V _{SD}	—	—	-1.2	V
Input Capacitance 输入电容 (V _{GS} =0V, V _{DS} = -10V, f=1MHz)	C _{ISS}	—	1010	—	pF
Common Source Output Capacitance 共源输出电容(V _{GS} =0V, V _{DS} = -10V, f=1MHz)	C _{OSS}	—	135	—	pF
Reverse Transfer Capacitance 反馈电容(V _{GS} =0V, V _{DS} = -10V, f=1MHz)	C _{RSS}	—	109	—	pF
Total Gate Charge 栅极电荷密度 (V _{DS} = -10V, I _D = -4A, V _{GS} = -4.5V)	Q _g	—	11	—	nC
Gate Source Charge 栅源电荷密度 (V _{DS} = -10V, I _D = -4A, V _{GS} = -4.5V)	Q _{gs}	—	2	—	nC
Gate Drain Charge 栅漏电荷密度 (V _{DS} = -10V, I _D = -4A, V _{GS} = -4.5V)	Q _{gd}	—	2	—	nC
Turn-ON Delay Time 开启延迟时间 (V _{DS} = -10V I _D = -1A, R _{GEN} =2.5 Ω, V _{GS} = -4.5V)	t _{d(on)}	—	8	—	ns
Turn-ON Rise Time 开启上升时间 (V _{DS} = -10V I _D = -1A, R _{GEN} =2.5 Ω, V _{GS} = -4.5V)	t _r	—	36	—	ns
Turn-OFF Delay Time 关断延迟时间 (V _{DS} = -10V I _D = -1A, R _{GEN} =2.5 Ω, V _{GS} = -4.5V)	t _{d(off)}	—	78	—	ns
Turn-OFF Fall Time 关断下降时间 (V _{DS} = -10V I _D = -1A, R _{GEN} =2.5 Ω, V _{GS} = -4.5V)	t _f	—	55	—	ns

■ Typical Characteristic Curve 典型特性曲线




Figure 1: Output Characteristics




Figure 2: Transfer Characteristics




Figure 3: On-Resistance vs. Drain Current




Figure 4: On-Resistance vs. Temperature




Figure 5: Capacitance Characteristics




Figure 6: Gate-Charge Characteristics

■ Typical Characteristic Curve 典型特性曲线




Figure 7: Drain Current vs. Temperature




Figure 8: Safe Operating Area





Figure 9: Transient Thermal Response Curve

■ **Dimension 外形封装尺寸**



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.900	1.00	0.035	0.039
e1	1.800	2.000	0.071	0.079
L	0.450	0.650	0.018	0.026
L1	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°