





NOTES:

1. CURRENT RATING:
3.0A MAX.
2. DIELECTRIC WITHSTAND VOLTAGE:
100VAC.
3. TEMPERATURE RANGE:
-30 °C ~ 85 °C.
4. CONTACT RESISTANCE:
40 MILLIONHM MAX.
5. INSULATION RESISTANCE:
100 MEGOHMS MIN.
6. INSERTION FORCE :
5N~20N.
7. UNMATING FORCE:
8N~20N.
8. DURABILITY:
10,000 CYCLES.
9. ALL PRODUCTS COMPLY WITH RoHS
ENVIRONMENTAL REQUIREMENTS.
- 10: MARK "▼" AS THE FOCUS,
FIRST ITEM INSPECTION.
- 11: MARK "⊗" TO MEASURE DIMENSIONS
FOR FAI.




A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS			GND
	RX1+	RX1-									
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

TABLE:

		SHELL		Stainless Steel,T=0.15mm;	Ni:50u"Min
		LATCH		Stainless Steel,T=0.3mm;	Electroplated semi-nickel matte tin;50u"Min;
		INSERT MOLD	EMC SPRING	Stainless Steel,T=0.10mm	-----
			CONTACT	Copper Alloy,T=0.20mm	Ni:50u"Min; Au:CONTACT AREA:1u", Solder AREA:Sn 50-100u"
			PLASTIC	LCP(G.F30%) BLACK.	-----
P/N	PART NAME	MATERIALS		FINISH	



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB TYPE C 公头12P(10-2P)单排SMT拉伸款有插脚有焊	
 UNIT: mm [inch]				CHECKED BY: 马跃	DATE : 2014-02-23
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO: HYC-2512301636	
SCALE:1:1	SIZE: A4			SHEET NO. 1 OF 1	