


## SOT-23 Bipolar Transistor 双极型三极管

### ■Features 特点

NPN High Frequency 高频



### ■Absolute Maximum Ratings 最大额定值

| Characteristic 特性参数                         | Symbol 符号              | Rat 额定值               | Unit 单位       |
|---------------------------------------------|------------------------|-----------------------|---------------|
| Collector-Base Voltage 集电极基极电压              | $V_{CBO}$              | 30                    | V             |
| Collector-Emitter Voltage 集电极发射极电压          | $V_{CEO}$              | 25                    | V             |
| Emitter-Base Voltage 发射极基极电压                | $V_{EBO}$              | 3                     | V             |
| Collector Current 集电极电流                     | $I_C$                  | 50                    | mA            |
| Power dissipation 耗散功率                      | $P_C(T_a=25^{\circ}C)$ | 225                   | mW            |
| Thermal Resistance Junction-Ambient 热阻      | $R_{\theta JA}$        | 556                   | $^{\circ}C/W$ |
| Junction and Storage Temperature<br>结温和储藏温度 | $T_J, T_{stg}$         | -55to+150 $^{\circ}C$ |               |

### ■Device Marking 产品打标







MMBTH10=3EM

**■Electrical Characteristics 电特性**


(TA=25℃ unless otherwise noted 如无特殊说明, 温度为 25℃)

| Characteristic<br>特性参数                                                         | Symbol<br>符号         | Min<br>最小值 | Type<br>典型值 | Max<br>最大值 | Unit<br>单位 |
|--------------------------------------------------------------------------------|----------------------|------------|-------------|------------|------------|
| Collector-Base Breakdown Voltage<br>集电极基极击穿电压<br>(IC=100μA, IE=0)              | BV <sub>CBO</sub>    | 30         | —           | —          | V          |
| Collector-Emitter Breakdown Voltage<br>集电极发射极击穿电压<br>(IC=1mA, IB=0)            | BV <sub>CEO</sub>    | 25         | —           | —          | V          |
| Emitter-Base Breakdown Voltage<br>发射极基极击穿电压<br>(IE=10μA, IC=0)                 | BV <sub>EBO</sub>    | 3          | —           | —          | V          |
| Collector-Base Leakage Current<br>集电极基极漏电流<br>(V <sub>CB</sub> =25V, IE=0)     | I <sub>CBO</sub>     | —          | —           | 100        | nA         |
| Collector-Emitter Leakage Current<br>集电极发射极漏电流<br>(V <sub>CE</sub> =20V, IE=0) | I <sub>CEO</sub>     | —          | —           | 100        | nA         |
| Emitter-Base Leakage Current<br>发射极基极漏电流<br>(V <sub>EB</sub> =2V, IC=0)        | I <sub>EBO</sub>     | —          | —           | 100        | nA         |
| DC Current Gain<br>直流电流增益<br>(V <sub>CE</sub> =10V, IC=4mA)                    | H <sub>FE</sub>      | 100        | —           | 200        |            |
| Collector-Emitter Saturation Voltage<br>集电极发射极饱和压降<br>(IC=4mA, IB=0.4mA)       | V <sub>CE(sat)</sub> | —          | —           | 0.5        | V          |
| Base-Emitter Saturation Voltage<br>基极发射极导通压降<br>(V <sub>CE</sub> =10V, IC=4mA) | V <sub>BE(on)</sub>  | —          | —           | 0.95       | V          |
| Transition Frequency<br>特征频率<br>(V <sub>CE</sub> =10V, IC=4mA)                 | f <sub>T</sub>       | 650        | —           | —          | MHz        |
| Output Capacitance<br>输出电容<br>(V <sub>CB</sub> =10V, IE=0, f=1MHz)             | C <sub>ob</sub>      | —          | —           | 0.7        | pF         |

■ Typical Characteristic Curve 典型特性曲线



■Dimension 外形封装尺寸



| Symbol   | Dimensions In Millimeters |       | Dimensions In Inches |       |
|----------|---------------------------|-------|----------------------|-------|
|          | Min                       | Max   | Min                  | Max   |
| A        | 0.900                     | 1.150 | 0.035                | 0.045 |
| A1       | 0.000                     | 0.100 | 0.000                | 0.004 |
| A2       | 0.900                     | 1.050 | 0.035                | 0.041 |
| b        | 0.300                     | 0.500 | 0.012                | 0.020 |
| c        | 0.080                     | 0.150 | 0.003                | 0.006 |
| D        | 2.800                     | 3.000 | 0.110                | 0.118 |
| E        | 1.200                     | 1.400 | 0.050                | 0.055 |
| E1       | 2.250                     | 2.550 | 0.089                | 0.100 |
| e        | 0.900                     | 1.00  | 0.035                | 0.039 |
| e1       | 1.800                     | 2.000 | 0.071                | 0.079 |
| L        | 0.500                     | 0.600 | 0.020                | 0.024 |
| L1       | 0.300                     | 0.500 | 0.012                | 0.020 |
| $\theta$ | 0°                        | 8°    | 0°                   | 8°    |