








3D VIEW



NOTES

(1) MATERIAL: SUS-301 THICKNESS=0.15mm

(2) PRODUCT SPECIFICATIONS:

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.50V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: CLAMPING FORCE: 40-120g

2-5: WELDING THRUST: ≥3KG

2-6: OPERATING TEMPERATURE: -40°C~+85°C

2-7: DURABILITY: 500 CYCLES


(3): SALT SPRAY: 24 HOURS

(4): FINISH: 50u"Min NICKEL UNDERPLATING OVER ALL.

(5): REQUIREMENTS

5-1: TERMINAL TO EAT FULL TIN, NOT PEELING

WELDING OBVIOUS COLOR AND OTHER ADVERSE

5-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS

RECOMMENDED PCB LAYOUT

TOLERANCE ±0.05 (焊盘推荐图)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 屏蔽罩固定夹 0.89H	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-PBJX09AX
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2601191603
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1