





订单号

台数



*实物不含光电传感器，仅做图纸效果

	中空旋转平台技术参数 Technical parameters of planetary reducer					中空旋转平台 hollow rotating platform					DTN130-10R									
描 图	减速比 reduction ratio		10																	
	旋转平台轴承 Rotary platform bearing		交叉滚子轴承 cross roller bearing																	
	容许轉矩 Allowable torque		40Nm	精度寿命 Precision life										20000h（间歇运转）		标记	处数	更改文件名	签 字	日 期
校 描	容许轴向负载 Allowable axial load		2000N	润滑方式 lubricating system										长效润滑		设 计				
	容许惯性力矩 Allowable moment of inertia		50Nm	匹配电机 Matching motor		各伺服品牌200/400W及57步进电机		校 对												
旧底图总号	允许盘面转速 Allowable disk speed		200r/min	光电开关 Photoelectric switch		选配		核 准												
	定位精度 positioning accuracy		≤1arcmin	安装方式 Installation mode		任意角度		标 准												
	重复定位精度 Repetitive positioning accuracy		≤10arcsec																	
日 期	旋转平台平行度 Rotation parallelism of platform		≤0.02mm										注意事项(Notice) 1. 本产品为精密零部件，应放置于干燥的地方保管。 The product is a precise part and it should be stored in a dry place. 2. 装配前应先应该检查电机与行星减速机各部位连接的尺寸,然后将减速机与电机自然连接。 Before assembling, the size of the connection between the motor and the parts of the gearbox reducer should be checked, Then the reducer is naturally connected to the motor. 3. 禁止使用铁锤等重物击打, 从而造成轴向力与径向力过大破坏轴承与齿轮。 It is forbidden to hit with hammer or other heavy objects It can cause damage to bearings and gears.							
	旋转平台同心度 Concentricity of rotating platform		≤0.01mm																	
	旋转平台台面偏差 Table deviation of rotating platform		≤0.01mm																	
签 字	噪音值 Noise value		≤63db																	
	保护等级 protect grade		IP40																	
	重量 weight		2.5KG																	