





0.08 A

(T=0.15)
-A-

NOTES:

- (1) MATERIAL: STAINLESS STEEL THICKNESS=0.15MM
(2) PRODUCT SPECIFICATIONS:
2-1: CONTACT RESISTANCE: 80mΩ/MAX
2-2: RATED CURRENT: 1.0A/MAX
2-3: VOLTAGE RATING: 1.50V/AC/DC/MAX
2-4: WELDING THRUST: ≥3KG
2-6: OPERATING TEMPERATURE: -40°C~+85°C
(3) SALT SPRAY: 24 HOURS
(4) FINISH: 50μMIN NICKEL UNDER PLATING OVER ALL
(5) REQUIREMENTS
5-1: TERMINAL TO EAT FULL TIN, NOT PEELING,
WELDING OBVIOUS COLOR AND OTHER ADVERSE
5-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT

TOLERANCE: ±0.05 (焊盘推荐图)



深圳市华宇创精密电子有限公司

TOLERANCE:

x.x ±0.30
x.xx ±0.25
x.xxx ±0.15
x.' ±2" x.x' ±0.5"



UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

H1.65mm 线夹

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW10-16B-165B

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2601191651

SHEET NO.

1 OF 1