










Dec.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Recommended PCB Layout
 (Board thickness : t=1.6±0.1mm)



Packaging Figure (3PINs)
 (FREE)
 340 ±1



- Note 1. 96 Pieces / Tray
 2. Refer to the technical specification (ETAP-H0816-00) for the packaging type.
 3. Refer to the technical specification (ETAP-H0654-00) in handling this product.
 4. UL (File No. E52653)
 C-UL (File No. E52653)
 TÜV (Certificate No. R50400864) authorization article.



1	PBT	BLACK, UL94-V0	3	PS	White		
2	Copper Alloy		2	Copper Alloy	Contact area : Au plating 0.2µmMIN Lead area : Sn plating 1µmMIN Under plating : Ni plating 1µmMIN		
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS		
UNITS mm		SCALE 2:1	COUNT 1	DESCRIPTION OF REVISIONS DIS-H-00020310	DESIGNED TS. KUMAZAWA	CHECKED SZ. ONO	DATE 2024. 04. 04
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : SJ. OKAMURA 2022. 08. 04	DRAWING NO. EDC-386586-50-00				
		CHECKED : TT. OHSAKO 2022. 08. 04	PART NO. DF60F-2P-10. 16DSA (50)				
		DESIGNED : SN. MIWA 2022. 08. 02	CODE NO. CL0680-4007-0-50				
		DRAWN : SN. MIWA 2022. 08. 02					