




REV.	ECN.NO.	MODIFY.CONTENT	DATE
A		NEW	2011/10/31





RECOMMENDED PCB LAYOUT
TOLERANCES ±0.05

NOTES


- Electrical:
Contact resistance:50m ohms max.
Dielectric withstanding voltage:500V RMS.
Insulation resistance:1000M ohms min.
- Mechanical:
MATE AND UNMATE FORCE:
MATE FORCE:4.5kg MAX
UNMATE FORCE:0.5kg MIN
Durability:1500cycles MIN.
- Environment:
Operating Temperature:-25°to+85°.
- FINISH:
TERMINAL: GOLD Plated Over NICKEL
Contact area,TIN ON
SOLDER TAIL AREA& TIN
Plated ALL Over NICKEL.
Shell: SPCC WITH NICKEL&GOLD Plated.

5.COLOR:
HOUSING:BLACK.



序号	DIM A	料号
1	2.65H	5001B-TF265-042
2	2.85H	5001B-TF285-043
3	3.00H	5001B-TF300-044
4	3.35H	5001B-TF335-045
5	3.75H	5001B-TF375-046
6	5.20H	5001B-TF520-047

Pin No.	NAME
1	DAT2
2	CD/DAT3
3	CMD
4	VDD
5	CLK
6	VSS
7	DAT0
8	DAT1



GENERAL TOLERANCE			DWG NO.		APPD:	WIND	Scale	1:1
X.±0.45	x.°±5°	Title	短型 T CARD 无侦测		CHKD:		UNIT	mm
.X±0.35	.x°±2°				DR:			
.XX±0.25	.xx°±1°	Part NO.	5001B-TF335-045		Date	2012/08/10		
.XXX±0.15	.xxx°±0.5°				东莞市文章济美电子有限公司			
SHEET	1/1							