









PROPRIETARY INFORMATION  
COMPANY CONFIDENTIAL

| REV. | ECN. NO. | DESCRIPTION | ENG | DATE |
|------|----------|-------------|-----|------|
|      |          |             |     |      |



3D VIEW



UNLESS OTHERWISE  
SPECIFIED TOLERANCES



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

|      |             |      |                                                                                                                     |          |
|------|-------------|------|---------------------------------------------------------------------------------------------------------------------|----------|
| 7    | HOUSING     | 1    | HIGHT TEMPERATURE PLASTIC COLOR BLACK                                                                               |          |
| 6    | TERMINAL 6# | 1    | COPPER ALLOY; NICKEL UNDER PLATING OVERALL,GOLD FLASH PLATING ON SOLDER AREA                                        | T=0.20mm |
| 5    | TERMINAL 5# | 1    | COPPER ALLOY; NICKEL UNDER PLATING OVERALL,GOLD FLASH PLATING ON SOLDER AREA                                        | T=0.20mm |
| 4    | TERMINAL 4# | 1    | STAINLESS STEEL; NICKEL UNDER PLATING OVERALL,GOLD FLASH PLATING ON SOLDER AREA ;GOLD FLASH PLATING ON CONTACT AREA | T=0.20mm |
| 3    | TERMINAL 3# | 1    | COPPER ALLOY; NICKEL UNDER PLATING OVERALL,GOLD FLASH PLATING ON SOLDER AREA ;GOLD FLASH PLATING ON CONTACT AREA    | T=0.20mm |
| 2    | TERMINAL 2# | 1    | COPPER ALLOY; NICKEL UNDER PLATING OVERALL,GOLD FLASH PLATING OVERALL;                                              | T=0.20mm |
| 1    | TERMINAL 1# | 1    | COPPER ALLOY; NICKEL UNDER PLATING OVERALL,GOLD FLASH PLATING OVERALL;                                              | T=0.20mm |
| ITEM | NAME        | Q'TY | DESCRIPTION                                                                                                         | NOTE     |

|           |       |         |     |          |  |                                                                |
|-----------|-------|---------|-----|----------|--|----------------------------------------------------------------|
| DECIMALS: |       | ANGLES: |     | DWG NO.  |  | PART NAME:<br>Ø3.5mm PHONE JACK H=4.5 mm<br>SMT TYPE CONNECTOR |
| DIM       | TOL   | DIM     | TOL | DESIGN:  |  |                                                                |
| X.        | ±0.50 | X.      | ±2° | CHECK:   |  |                                                                |
| X.X       | ±0.30 | X.X     | ±1° |          |  | PART NO.<br>PJ35A063-F06G1BR-A                                 |
| X.XX      | ±0.20 | X.XX    |     | APPROVED |  | REV. UNIT: SHEET:                                              |
| X.XXX     | ±0.10 | X.XXX   |     |          |  | A mm 1/1                                                       |