






REV.	ECN.NO.	MODIFY.CONTENT	DATE
A0		NEW	2011/12/31




RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05



- 1.Electrical Characteristics:
Current Rating:1.5A.
Withstanding Voltage:AC500V r.m.s.
Insulation Resistance:1000Megohms Minimum at DC 500V
Contact Resistance:100Miliohms Maximum.
- 2.Mechanical Characteristics:
Mating Cycles:3000 Insertions.
- 3.Environmental:
Operating Temperature:-25°To+70°
- 4.Material:
1.Housing:HI-Temp plastic UL 94V-0 Rated.
2.Contact:Copper Alloy.
3.Shell:SUS.
- 5.Finish :
1u" Gold plated on conatct area,1u"Min Au plated on solder tails, Base Nickel :50u"Min
- 6.Packing:
Number of connectors:750Pcs/REEL



Connector terminal NO.	Pin NO.	GENERAL TOLERANCE		DWG NO.		APPD:		Scale	1:1
Pin 1	VCC:PWR signal and GND	X.±0.45	x.'±5°	Title	SIM CARD PUSH PUSH 6P (顺向) TYPE2	CHKD:		UNIT	mm
Pin 2	RST:Reset signal	.X±0.35	.x'±2°			DR:		Visual	
Pin 3	CLK:Clocking signal	.XX±0.25	.xx'±1°	Part NO.	5001B-SIM185-041	Date	2011/12/31	Edition	A1
Pin 5	GND:PWR signal and GND	.XXX±0.15	.xxx'±0.5°					东莞市文章济美电子有限公司	
Pin 6	VPP:Porgramming Voltage								
Pin 7	I/O:Serial date input/output	SHEET	1/2						

REV.	ECN.NO.	MODIFY.CONTENT	DATE
A0		初版发行	2011.12.31




<TABLE 1> PACKAGING QUANTITY

QTY/REEL	REEL/CARTON	QTY/CARTON
750	6	3300




COVER TAPE PEELING FORCE:50gf~150gf



NOTE:

1. 依<图一>示放置产品于下载中, 每穴放置1PCS产品.
2. 包装机包好后, 在REEL的个等分点贴上胶带, 以防止REEL张开, 每REEL贴1PCS标签, 如<图二>示
3. 包装数量见如<TABLE 1>示
4. 包装成箱见如<图三>示
箱底放保丽龙板, 再依次将指定数量的卷装产品放入箱内, 四角分别放入四个三角护板, 最上层再放上保丽龙板.
5. 封箱, 在封好的纸箱上按客户要求写上料号, 数量等



GENERAL TOLERANCE		图 号			设 计		比 例	1:1
X±0.45	x.°±5°	品 名			审 核		单 位	mm
.X±0.35	.x°±2°		核 准					
.XX±0.25	.xx°±1°	料 号	5001B-SIM185-041	日 期		2011/12/31		
.XXX±0.15	.xxx°±0.5°		东莞市文章济美电子有限公司					
页号	2/2							