



PIN NO.	PIN ASSIGNMENT
P1	DAT2
P2	CD/DAT3
P3	CMD
P4	VDD
P5	CLK
P6	VSS
P7	DAT0
P8	DAT1



RECOMMEND P.C.B LAYOUT
(General tolerance ±0.05)



△ Specification

- 1.MATERIAL:
- 1.1 Insulator:High Temperature Thermoplastic, LCP SZ6505HF black UL94V-0.
 - 1.2 Terminal: Phosphor Bronze(C5210-H, T=0.15mm) △
 - 1.3 Shell: SUS301-3/4H T=0.10mm
 - 1.4 Spring: SUS301 L=9.80mm
 - 1.5 Slider: PA9T black △
 - 1.6 Drawbar: SUS304-H,L=3.85mm
- 2.Plating:
- 2.1 Terminal: Plated 80u"min Ni Overall
Plated 1u"min Au Selective contact area
Plated 1u"min AU over Ni on solder area
 - 2.2 Shell: Plated 1u"min AU overll 50u"min Ni
- 3.Property:
- 3.1 Current Rating :0.5A AC/DC max.
 - 3.2 Voltage Rating :12V AC/DC
 - 3.3 Ambient Temperature Range :-20°C~+60°C
 - 3.4 Ambient Humidity Range :95% R.H. Max.
 - 3.5 Contact Resistance:100mΩ max.
 - 3.6 Insulation Resistance:1000MΩ min./500VDC
 - 3.7 Durability:5000 cycles

LXW 连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: TF PUSH 内焊1.28H	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. LXW-TF-128	MOLD NO.
UNIT: mm [inch]	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	SHEET NO. 1 OF 1
SCALE:1:1	SIZE: A4			