






REV.	ECN.NO.	MODIFY.CONTENT	DATE
A		NEW	2018/11/29



NO PATTERN AREA
NO CIRCUIT AREA
SOLDER AREA

P.C.B. LAYOUT
(TOLERANCE±0.05)



NOTE:

一.材质及电镀方式 (MATERIAL AND FINISH)

- 塑胶 (HOUSING):LCP,
UL 94V-0 , COLOR:BLACK
- 端子 (CONTACT):COPPER ALLOY
GOLD FLASH PLATING ON CONTACT AREA,
GOLD FLASH PLATING ON SOLDER TAILS
50u" NICKEL UNDER PLATING OVER ALL
- 铁壳 (SHELL):SUS304-3/4H
40u" NICKEL UNDER PLATING OVER ALL

二.机械特性 (MECHANICAL CHARACTERISTICS)

- 插入力 (Insertion Force):2.0Kgf Max
- 拔出力 (Withdrawal Force):0.1Kgf Min
- 耐久性 (Durability):5000次


三.电气特性

- 额定电流 (Current rating):1.0A AC/DC
- 接触电阻 (Contact resistance):100mΩ MAX
- 绝缘电阻 (Insulation resistance):500MΩ MIN
- 适用温度 (Operating temperature):-20℃ ~65℃

TF CARD PIN ASSIGNMENT

PIN NO.	PIN ASSIGNMENT
T1	DAT2
T2	CD/DAT3 ²
T3	CMD
T4	VDD
T5	CLK
T6	VSS
T7	DAT0
T8	DAT1

SIM pin assignment	
	Name
C1	VCC
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	VPP
C7	I/O
C8	Reserved



GENERAL TOLERANCE				DWG NO.		APPD:	WIND	Scale	1:1
X.±0.45		x.*±5°		Title	2.28H 二合一卡座 平脚（缺口外壳）	CHKD:		UNIT	mm
.X±0.35		.x*±2°				DR:			
.XX±0.25		.xx*±1°		Part NO.	5001B-SIM228-192	Date	2018/11/29		
.XXX±0.15		.xxx*±0.5°				东莞市文章济美电子有限公司			
SHEET	1/1								